

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251188

Luminaire Tested: **LSR8B60D010 EC8B60935 8LBS0WH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251188  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B60D010 EC8B60935 8LBS0WH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
90 CRI 3500 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5941.0 lumens  
Efficiency: N/A  
Efficacy: 99.8 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251188

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBS0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P251188

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBS0WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	103767
5°	104164
10°	105475
15°	107536
20°	109072
25°	109520
30°	106165
35°	96900
40°	83821
45°	65989
50°	42566
55°	20892
60°	8591
65°	3765
70°	1082
75°	405
80°	302
85°	0



TEST NUMBER: P251188

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBS0WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	321.3	5.4
10°-20°	952.0	16.0
20°-30°	1473.9	24.8
30°-40°	1596.7	26.9
40°-50°	1149.0	19.3
50°-60°	384.4	6.5
60°-70°	58.1	1.0
70°-80°	5.0	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2747.2	46.2
0°-40°	4343.8	73.1
0°-60°	5877.2	98.9
0°-90°	5941.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5941.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3365	
5°	3365	321
15°	3368	952
25°	3219	1474
35°	2574	1597
45°	1513	1149
55°	389	384
65°	52	58
75°	3	5
85°	0	1
90°	0	



TEST NUMBER: P251188

CATALOG NUMBER: LSR8B60D010 EC8B60935 8LBS0WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3365.1
2.5°	3365.1
5°	3365.1
7.5°	3366.8
10°	3368.5
12.5°	3371.9
15°	3368.5
17.5°	3354.7
20°	3323.8
22.5°	3277.4
25°	3218.9
27.5°	3126.0
30°	2981.6
32.5°	2792.5
35°	2574.1
37.5°	2338.5
40°	2082.3
42.5°	1807.2
45°	1513.2
47.5°	1195.1
50°	887.3
52.5°	608.7
55°	388.6
57.5°	232.1
60°	139.3
62.5°	84.3
65°	51.6
67.5°	25.8
70°	12.0
72.5°	5.2
75°	3.4
77.5°	3.4
80°	1.7
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)