

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243966

Luminaire Tested: **LD8B10D010 ER8B10850 8LBMOLI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P243966  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-11)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B10D010 ER8B10850 8LBM0LI  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 5000 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1190.1 lumens  
Efficiency: N/A  
Efficacy: 116.7 lumens/watt  
Spacing Criteria (0/90/45): 0.63 / 0.63 / 0.72  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P243966

CATALOG NUMBER: LD8B10D010 ER8B10850 8LBM0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P243966

CATALOG NUMBER: LD8B10D010 ER8B10850 8LBM0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	73	80	75	72		79	75	72		77	74	71	70
7	86	78	72	69	85	77	72	68	76	71	68		75	71	68		74	70	67	66
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	60	59
10	76	67	62	58	75	67	61	58	66	61	58		65	61	58		64	60	58	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	64013
5°	61261
10°	54539
15°	43816
20°	34318
25°	27709
30°	21471
35°	12231
40°	4613
45°	1989
50°	801
55°	301
60°	160
65°	109
70°	63
75°	48
80°	0
85°	0



TEST NUMBER: P243966

CATALOG NUMBER: LD8B10D010 ER8B10850 8LBM0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	181.7	15.3
10°-20°	381.1	32.0
20°-30°	372.9	31.3
30°-40°	206.3	17.3
40°-50°	40.0	3.4
50°-60°	6.1	0.5
60°-70°	1.5	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	935.7	78.6
0°-40°	1142.1	96.0
0°-60°	1188.1	99.8
0°-90°	1190.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1190.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2076	
5°	1979	182
15°	1372	381
25°	814	373
35°	325	206
45°	46	40
55°	6	6
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P243966

CATALOG NUMBER: LD8B10D010 ER8B10850 8LBM0LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2075.9
2.5°	2047.4
5°	1979.1
7.5°	1883.5
10°	1741.8
12.5°	1562.7
15°	1372.5
17.5°	1194.1
20°	1045.8
22.5°	923.0
25°	814.4
27.5°	712.0
30°	603.0
32.5°	475.0
35°	324.9
37.5°	195.4
40°	114.6
42.5°	71.6
45°	45.6
47.5°	28.6
50°	16.7
52.5°	9.3
55°	5.6
57.5°	3.3
60°	2.6
62.5°	1.9
65°	1.5
67.5°	1.1
70°	0.7
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)