

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250880

Luminaire Tested: **LSR8B60D010 EC8B60940 8LBSOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250880
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B60940 8LBS0LI
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 4000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6262.0 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250880

CATALOG NUMBER: LSR8B60D010 EC8B60940 8LBSOLI

Luminous Intensity Polar Plot





TEST NUMBER: P250880

CATALOG NUMBER: LSR8B60D010 EC8B60940 8LBSOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	99	95	91	103	98	93	90	94	91	88		91	88	86		88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78		84	80	77		82	78	75	74
4	92	83	76	71	90	82	75	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	63	84	75	68	63	73	67	63		71	66	62		69	65	61	60
6	80	70	62	57	79	69	62	57	67	61	56		66	60	56		64	59	56	54
7	75	64	57	52	74	63	56	52	62	56	51		61	55	51		59	54	51	49
8	71	59	52	47	69	58	52	47	57	51	47		56	51	46		55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43		52	47	43		51	46	42	41
10	62	51	44	39	61	50	44	39	50	43	39		49	43	39		48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107662
5°	108129
10°	109886
15°	112663
20°	114630
25°	114760
30°	111207
35°	101820
40°	88490
45°	70019
50°	45406
55°	22693
60°	9528
65°	4195
70°	1298
75°	643
80°	639
85°	637



TEST NUMBER: P250880

CATALOG NUMBER: LSR8B60D010 EC8B60940 8LBS0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	333.9	5.3
10°-20°	997.3	15.9
20°-30°	1544.9	24.7
30°-40°	1677.8	26.8
40°-50°	1219.2	19.5
50°-60°	414.4	6.6
60°-70°	66.0	1.1
70°-80°	7.1	0.1
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2876.1	45.9
0°-40°	4553.9	72.7
0°-60°	6187.5	98.8
0°-90°	6262.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6262.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3491	
5°	3493	334
15°	3529	997
25°	3373	1545
35°	2705	1678
45°	1606	1219
55°	422	414
65°	58	66
75°	5	7
85°	2	1
90°	0	



TEST NUMBER: P250880

CATALOG NUMBER: LSR8B60D010 EC8B60940 8LBSOLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3491.4
2.5°	3491.4
5°	3493.2
7.5°	3498.6
10°	3509.4
12.5°	3521.9
15°	3529.1
17.5°	3521.9
20°	3493.2
22.5°	3441.1
25°	3372.9
27.5°	3270.5
30°	3123.2
32.5°	2927.5
35°	2704.8
37.5°	2462.3
40°	2198.3
42.5°	1912.7
45°	1605.6
47.5°	1275.2
50°	946.5
52.5°	648.4
55°	422.1
57.5°	256.8
60°	154.5
62.5°	95.2
65°	57.5
67.5°	32.3
70°	14.4
72.5°	9.0
75°	5.4
77.5°	3.6
80°	3.6
82.5°	1.8
85°	1.8
87.5°	0.0
90°	0.0

(END OF REPORT)