

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245334

Luminaire Tested: **LD8B10D010 ER8B10850 8LBS0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245334
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10850 8LBS0WH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1228.0 lumens
Efficiency: N/A
Efficacy: 120.4 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245334

CATALOG NUMBER: LD8B10D010 ER8B10850 8LBS0WH

Luminous Intensity Polar Plot





TEST NUMBER: P245334

CATALOG NUMBER: LD8B10D010 ER8B10850 8LBS0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	21450
5°	21532
10°	21803
15°	22229
20°	22544
25°	22636
30°	21944
35°	20030
40°	17325
45°	13641
50°	8798
55°	4317
60°	1776
65°	781
70°	225
75°	83
80°	71
85°	0



TEST NUMBER: P245334

CATALOG NUMBER: LD8B10D010 ER8B10850 8LBS0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.4	5.4
10°-20°	196.8	16.0
20°-30°	304.6	24.8
30°-40°	330.0	26.9
40°-50°	237.5	19.3
50°-60°	79.5	6.5
60°-70°	12.0	1.0
70°-80°	1.0	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	567.8	46.2
0°-40°	897.9	73.1
0°-60°	1214.8	98.9
0°-90°	1228.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1228.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	696	
5°	696	66
15°	696	197
25°	665	305
35°	532	330
45°	313	237
55°	80	79
65°	11	12
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P245334

CATALOG NUMBER: LD8B10D010 ER8B10850 8LBS0WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	695.6
2.5°	695.6
5°	695.6
7.5°	695.9
10°	696.3
12.5°	697.0
15°	696.3
17.5°	693.4
20°	687.0
22.5°	677.4
25°	665.3
27.5°	646.2
30°	616.3
32.5°	577.2
35°	532.1
37.5°	483.4
40°	430.4
42.5°	373.5
45°	312.8
47.5°	247.0
50°	183.4
52.5°	125.8
55°	80.3
57.5°	48.0
60°	28.8
62.5°	17.4
65°	10.7
67.5°	5.3
70°	2.5
72.5°	1.1
75°	0.7
77.5°	0.7
80°	0.4
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)