

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246558

Luminaire Tested: **LD8B10D010 ER8B10850 8LBW0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246558
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-48)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10850 8LBW0MW
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1171.0 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246558

CATALOG NUMBER: LD8B10D010 ER8B10850 8LBW0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246558

CATALOG NUMBER: LD8B10D010 ER8B10850 8LBW0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	86	83	80	78
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62
5	84	73	66	60	82	72	65	60	70	64	59	68	63	59	67	62	58	56
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47
8	69	58	50	45	68	57	50	45	56	50	45	55	49	45	54	48	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	40
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	23926
5°	23522
10°	22783
15°	22254
20°	21937
25°	21507
30°	20193
35°	16484
40°	10212
45°	6916
50°	6093
55°	5752
60°	5705
65°	5531
70°	4959
75°	4289
80°	3623
85°	2901



TEST NUMBER: P246558

CATALOG NUMBER: LD8B10D010 ER8B10850 8LBW0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.5	6.1
10°-20°	196.9	16.8
20°-30°	288.7	24.7
30°-40°	263.9	22.5
40°-50°	130.7	11.2
50°-60°	96.7	8.3
60°-70°	74.3	6.3
70°-80°	38.7	3.3
80°-90°	9.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	557.1	47.6
0°-40°	821.1	70.1
0°-60°	1048.4	89.5
0°-90°	1171.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1171.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	776	
5°	760	71
15°	697	197
25°	632	289
35°	438	264
45°	159	131
55°	107	97
65°	76	74
75°	36	39
85°	8	10
90°	0	



TEST NUMBER: P246558

CATALOG NUMBER: LD8B10D010 ER8B10850 8LBW0MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	775.9
2.5°	771.8
5°	759.9
7.5°	743.9
10°	727.6
12.5°	711.6
15°	697.1
17.5°	683.4
20°	668.5
22.5°	651.8
25°	632.1
27.5°	605.0
30°	567.1
32.5°	514.0
35°	437.9
37.5°	343.6
40°	253.7
42.5°	192.0
45°	158.6
47.5°	140.4
50°	127.0
52.5°	116.3
55°	107.0
57.5°	99.2
60°	92.5
62.5°	85.4
65°	75.8
67.5°	65.4
70°	55.0
72.5°	45.3
75°	36.0
77.5°	27.9
80°	20.4
82.5°	14.1
85°	8.2
87.5°	3.0
90°	0.0

(END OF REPORT)