

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251192

Luminaire Tested: **LSR8B60D010 EC8B60950 8LBS0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251192
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B60950 8LBS0WH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 5000 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6424.0 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251192

CATALOG NUMBER: LSR8B60D010 EC8B60950 8LBS0WH

Luminous Intensity Polar Plot





TEST NUMBER: P251192

CATALOG NUMBER: LSR8B60D010 EC8B60950 8LBS0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57		66	60	56		64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47		56	51	47		55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43		52	47	43		51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39		49	43	39		48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	112201
5°	112630
10°	114051
15°	116280
20°	117938
25°	118424
30°	114796
35°	104779
40°	90636
45°	71353
50°	46025
55°	22591
60°	9288
65°	4071
70°	1172
75°	441
80°	337
85°	0



TEST NUMBER: P251192

CATALOG NUMBER: LSR8B60D010 EC8B60950 8LBS0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	347.5	5.4
10°-20°	1029.4	16.0
20°-30°	1593.7	24.8
30°-40°	1726.5	26.9
40°-50°	1242.4	19.3
50°-60°	415.7	6.5
60°-70°	62.8	1.0
70°-80°	5.4	0.1
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2970.5	46.2
0°-40°	4697.0	73.1
0°-60°	6355.0	98.9
0°-90°	6424.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6424.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3639	
5°	3639	347
15°	3642	1029
25°	3481	1594
35°	2783	1726
45°	1636	1242
55°	420	416
65°	56	63
75°	4	5
85°	0	1
90°	0	



TEST NUMBER: P251192

CATALOG NUMBER: LSR8B60D010 EC8B60950 8LBS0WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3638.6
2.5°	3638.6
5°	3638.6
7.5°	3640.5
10°	3642.4
12.5°	3646.1
15°	3642.4
17.5°	3627.5
20°	3594.0
22.5°	3543.8
25°	3480.6
27.5°	3380.2
30°	3224.0
32.5°	3019.5
35°	2783.4
37.5°	2528.6
40°	2251.6
42.5°	1954.1
45°	1636.2
47.5°	1292.2
50°	959.4
52.5°	658.2
55°	420.2
57.5°	251.0
60°	150.6
62.5°	91.1
65°	55.8
67.5°	27.9
70°	13.0
72.5°	5.6
75°	3.7
77.5°	3.7
80°	1.9
82.5°	1.9
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)