

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251098

Luminaire Tested: **LSR8B60D010 EC8B60950 8LBS0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251098  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B60D010 EC8B60950 8LBS0WMH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
90 CRI 5000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6182.0 lumens  
Efficiency: N/A  
Efficacy: 103.9 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251098

CATALOG NUMBER: LSR8B60D010 EC8B60950 8LBS0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P251098

CATALOG NUMBER: LSR8B60D010 EC8B60950 8LBS0W/MH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55	64	58	54	63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	108084
5°	107748
10°	106783
15°	105723
20°	104586
25°	102937
30°	100108
35°	95548
40°	88551
45°	74763
50°	51293
55°	28289
60°	14222
65°	8004
70°	4355
75°	3098
80°	1989
85°	1309



TEST NUMBER: P251098

CATALOG NUMBER: LSR8B60D010 EC8B60950 8LBS0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	330.0	5.3
10°-20°	934.0	15.1
20°-30°	1390.5	22.5
30°-40°	1579.6	25.6
40°-50°	1291.2	20.9
50°-60°	506.0	8.2
60°-70°	117.9	1.9
70°-80°	28.4	0.5
80°-90°	4.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2654.5	42.9
0°-40°	4234.0	68.5
0°-60°	6031.1	97.6
0°-90°	6182.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6182.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3505	
5°	3481	330
15°	3312	934
25°	3025	1391
35°	2538	1580
45°	1714	1291
55°	526	506
65°	110	118
75°	26	28
85°	4	5
90°	0	



TEST NUMBER: P251098

CATALOG NUMBER: LSR8B60D010 EC8B60950 8LBS0WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3505.1
2.5°	3499.5
5°	3480.9
7.5°	3449.3
10°	3410.3
12.5°	3361.9
15°	3311.7
17.5°	3252.2
20°	3187.1
22.5°	3110.9
25°	3025.4
27.5°	2924.9
30°	2811.5
32.5°	2683.2
35°	2538.2
37.5°	2378.3
40°	2199.8
42.5°	1984.1
45°	1714.4
47.5°	1398.3
50°	1069.2
52.5°	768.0
55°	526.2
57.5°	344.0
60°	230.6
62.5°	158.1
65°	109.7
67.5°	72.5
70°	48.3
72.5°	33.5
75°	26.0
77.5°	18.6
80°	11.2
82.5°	5.6
85°	3.7
87.5°	1.9
90°	0.0

(END OF REPORT)