

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244362

Luminaire Tested: **LD8B10D010 ER8B10927 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244362
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27944)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10927 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 819.0 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.79
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244362

CATALOG NUMBER: LD8B10D010 ER8B10927 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P244362

CATALOG NUMBER: LD8B10D010 ER8B10927 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 114 | 111 | 109 | 106 | 111 | 109 | 107 | 105 | 105 | 103 | 101 | | 101 | 100 | 98 | | 98 | 97 | 96 | 94 |
| 2 | 108 | 104 | 100 | 96 | 106 | 102 | 98 | 95 | 99 | 96 | 93 | | 96 | 93 | 91 | | 93 | 91 | 89 | 88 |
| 3 | 103 | 97 | 92 | 88 | 101 | 95 | 91 | 87 | 93 | 89 | 86 | | 90 | 87 | 85 | | 88 | 86 | 83 | 82 |
| 4 | 98 | 91 | 85 | 81 | 96 | 90 | 85 | 81 | 87 | 83 | 80 | | 85 | 82 | 79 | | 84 | 81 | 78 | 76 |
| 5 | 93 | 85 | 79 | 75 | 92 | 84 | 79 | 75 | 82 | 78 | 74 | | 81 | 77 | 74 | | 79 | 76 | 73 | 72 |
| 6 | 89 | 80 | 74 | 70 | 87 | 79 | 74 | 70 | 78 | 73 | 69 | | 76 | 72 | 69 | | 75 | 71 | 69 | 67 |
| 7 | 85 | 76 | 70 | 66 | 83 | 75 | 69 | 65 | 74 | 69 | 65 | | 72 | 68 | 65 | | 71 | 67 | 64 | 63 |
| 8 | 81 | 71 | 66 | 62 | 79 | 71 | 65 | 61 | 70 | 65 | 61 | | 69 | 64 | 61 | | 68 | 64 | 61 | 59 |
| 9 | 77 | 68 | 62 | 58 | 76 | 67 | 62 | 58 | 66 | 61 | 58 | | 65 | 61 | 58 | | 64 | 60 | 57 | 56 |
| 10 | 74 | 64 | 59 | 55 | 73 | 64 | 58 | 55 | 63 | 58 | 55 | | 62 | 58 | 54 | | 61 | 57 | 54 | 53 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 38552 |
| 5° | 35959 |
| 10° | 30996 |
| 15° | 26826 |
| 20° | 23335 |
| 25° | 20054 |
| 30° | 15760 |
| 35° | 9193 |
| 40° | 4243 |
| 45° | 2194 |
| 50° | 1103 |
| 55° | 538 |
| 60° | 271 |
| 65° | 161 |
| 70° | 72 |
| 75° | 71 |
| 80° | 36 |
| 85° | 0 |



TEST NUMBER: P244362

CATALOG NUMBER: LD8B10D010 ER8B10927 8LBN0H

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 105.1 | 12.8 |
| 10°-20° | 234.9 | 28.7 |
| 20°-30° | 267.1 | 32.6 |
| 30°-40° | 156.9 | 19.2 |
| 40°-50° | 42.1 | 5.1 |
| 50°-60° | 10.0 | 1.2 |
| 60°-70° | 2.2 | 0.3 |
| 70°-80° | 0.5 | 0.1 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 607.2 | 74.1 |
| 0°-40° | 764.1 | 93.3 |
| 0°-60° | 816.2 | 99.7 |
| 0°-90° | 819.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 819.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1250 | |
| 5° | 1162 | 105 |
| 15° | 840 | 235 |
| 25° | 589 | 267 |
| 35° | 244 | 157 |
| 45° | 50 | 42 |
| 55° | 10 | 10 |
| 65° | 2 | 2 |
| 75° | 1 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P244362

CATALOG NUMBER: LD8B10D010 ER8B10927 8LBN0H

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1250.2 |
| 1° | 1243.4 |
| 2° | 1230.5 |
| 3° | 1212.6 |
| 4° | 1189.4 |
| 5° | 1161.7 |
| 6° | 1130.4 |
| 7° | 1095.1 |
| 8° | 1059.6 |
| 9° | 1024.0 |
| 10° | 989.9 |
| 11° | 956.7 |
| 12° | 925.5 |
| 13° | 896.4 |
| 14° | 867.4 |
| 15° | 840.3 |
| 16° | 813.7 |
| 17° | 787.5 |
| 18° | 762.1 |
| 19° | 736.3 |
| 20° | 711.1 |
| 21° | 685.9 |
| 22° | 661.8 |
| 23° | 638.1 |
| 24° | 613.8 |
| 25° | 589.4 |
| 26° | 564.3 |
| 27° | 536.8 |
| 28° | 508.0 |
| 29° | 476.6 |
| 30° | 442.6 |
| 32.5° | 347.2 |
| 35° | 244.2 |
| 37.5° | 161.0 |
| 40° | 105.4 |
| 42.5° | 72.8 |
| 45° | 50.3 |
| 47.5° | 34.5 |
| 50° | 23.0 |
| 52.5° | 15.0 |
| 55° | 10.0 |
| 57.5° | 6.6 |
| 60° | 4.4 |
| 62.5° | 3.0 |
| 65° | 2.2 |



TEST NUMBER: P244362

CATALOG NUMBER: LD8B10D010 ER8B10927 8LBN0H

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|-----|
| 67.5° | 1.3 |
| 70° | 0.8 |
| 72.5° | 0.6 |
| 75° | 0.6 |
| 77.5° | 0.2 |
| 80° | 0.2 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)