

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251502

Luminaire Tested: **LSR8B60D010 EC8B609727 8LBS0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251502
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-18)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B609727 8LBS0MW
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 2700 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4825.0 lumens
Efficiency: N/A
Efficacy: 81.1 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251502

CATALOG NUMBER: LSR8B60D010 EC8B609727 8LBS0MW

Luminous Intensity Polar Plot





TEST NUMBER: P251502

CATALOG NUMBER: LSR8B60D010 EC8B609727 8LBS0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	98	96	97	95	93	94	92	91	89
2	103	97	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69
4	89	79	71	66	87	78	71	65	75	69	64	73	68	64	71	67	63	61
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P251502

CATALOG NUMBER: LSR8B60D010 EC8B609727 8LBS0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	236.4	4.9
10°-20°	665.7	13.8
20°-30°	990.2	20.5
30°-40°	1146.2	23.8
40°-50°	983.5	20.4
50°-60°	452.2	9.4
60°-70°	192.0	4.0
70°-80°	118.9	2.5
80°-90°	39.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1892.4	39.2
0°-40°	3038.5	63.0
0°-60°	4474.3	92.7
0°-90°	4825.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4825.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2516	
5°	2496	236
15°	2360	666
25°	2152	990
35°	1839	1146
45°	1307	984
55°	477	452
65°	188	192
75°	115	119
85°	35	40
90°	0	



TEST NUMBER: P251502

CATALOG NUMBER: LSR8B60D010 EC8B609727 8LBS0MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2515.5
2.5°	2509.9
5°	2495.8
7.5°	2472.0
10°	2439.7
12.5°	2401.8
15°	2359.7
17.5°	2314.7
20°	2265.6
22.5°	2212.3
25°	2151.9
27.5°	2084.5
30°	2011.5
32.5°	1930.1
35°	1838.9
37.5°	1740.6
40°	1625.5
42.5°	1483.7
45°	1306.9
47.5°	1089.3
50°	859.1
52.5°	645.7
55°	477.3
57.5°	350.9
60°	270.9
62.5°	221.8
65°	188.1
67.5°	161.4
70°	140.4
72.5°	127.7
75°	115.1
77.5°	98.3
80°	78.6
82.5°	56.1
85°	35.1
87.5°	15.4
90°	0.0

(END OF REPORT)