

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251194

Luminaire Tested: **LSR8B60D010 EC8B609727 8LBS0WH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251194  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B60D010 EC8B609727 8LBS0WH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 2700 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4850.0 lumens  
Efficiency: N/A  
Efficacy: 81.5 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251194

CATALOG NUMBER: LSR8B60D010 EC8B609727 8LBS0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P251194

CATALOG NUMBER: LSR8B60D010 EC8B609727 8LBS0WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P251194

CATALOG NUMBER: LSR8B60D010 EC8B609727 8LBS0WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	262.3	5.4
10°-20°	777.1	16.0
20°-30°	1203.2	24.8
30°-40°	1303.5	26.9
40°-50°	938.0	19.3
50°-60°	313.8	6.5
60°-70°	47.4	1.0
70°-80°	4.0	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2242.7	46.2
0°-40°	3546.2	73.1
0°-60°	4797.9	98.9
0°-90°	4850.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4850.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2747	
5°	2747	262
15°	2750	777
25°	2628	1203
35°	2101	1303
45°	1235	938
55°	317	314
65°	42	47
75°	3	4
85°	0	1
90°	0	



TEST NUMBER: P251194

CATALOG NUMBER: LSR8B60D010 EC8B609727 8LBS0WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2747.1
2.5°	2747.1
5°	2747.1
7.5°	2748.5
10°	2749.9
12.5°	2752.7
15°	2749.9
17.5°	2738.7
20°	2713.4
22.5°	2675.5
25°	2627.8
27.5°	2552.0
30°	2434.1
32.5°	2279.7
35°	2101.4
37.5°	1909.1
40°	1699.9
42.5°	1475.3
45°	1235.3
47.5°	975.6
50°	724.3
52.5°	496.9
55°	317.2
57.5°	189.5
60°	113.7
62.5°	68.8
65°	42.1
67.5°	21.1
70°	9.8
72.5°	4.2
75°	2.8
77.5°	2.8
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)