

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245586

Luminaire Tested: **LD8B10D010 ER8B10927 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245586
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10927 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 796.5 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245586

CATALOG NUMBER: LD8B10D010 ER8B10927 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245586

CATALOG NUMBER: LD8B10D010 ER8B10927 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92				92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84				84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70				70
5	88	79	72	67	87	78	72	67	76	71	66	74	70	66	73	69	65	64				64
6	83	73	66	61	82	72	66	61	71	65	61	69	64	60	68	63	60	58				58
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54				54
8	74	63	56	52	73	63	56	52	61	56	51	60	55	51	59	55	51	49				49
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46				46
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	43				43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	19125
5°	18672
10°	18089
15°	17823
20°	17615
25°	17237
30°	16144
35°	13183
40°	7870
45°	4727
50°	3406
55°	2317
60°	1455
65°	715
70°	180
75°	71
80°	53
85°	0



TEST NUMBER: P245586

CATALOG NUMBER: LD8B10D010 ER8B10927 8LBW0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.7	7.1
10°-20°	157.6	19.8
20°-30°	231.4	29.1
30°-40°	209.8	26.3
40°-50°	89.8	11.3
50°-60°	39.7	5.0
60°-70°	10.6	1.3
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	445.7	56.0
0°-40°	655.5	82.3
0°-60°	785.0	98.6
0°-90°	796.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	796.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	620	
5°	603	57
15°	558	158
25°	507	231
35°	350	210
45°	108	90
55°	43	40
65°	10	11
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P245586

CATALOG NUMBER: LD8B10D010 ER8B10927 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	620.2
2.5°	615.3
5°	603.2
7.5°	589.4
10°	577.7
12.5°	567.9
15°	558.3
17.5°	548.3
20°	536.8
22.5°	523.4
25°	506.6
27.5°	484.2
30°	453.4
32.5°	410.3
35°	350.2
37.5°	271.5
40°	195.5
42.5°	141.2
45°	108.4
47.5°	87.4
50°	71.0
52.5°	56.4
55°	43.1
57.5°	32.2
60°	23.6
62.5°	16.4
65°	9.8
67.5°	4.3
70°	2.0
72.5°	1.1
75°	0.6
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)