

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244440

Luminaire Tested: **LD8B10D010 ER8B10930 8LBM0H**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244440  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27951)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B10D010 ER8B10930 8LBM0H  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 915.9 lumens  
Efficiency: N/A  
Efficacy: 89.8 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 10.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244440

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBM0H

### Luminous Intensity Polar Plot





TEST NUMBER: P244440

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBM0H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86	83	80	79
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80	77	74	73
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75	72	69	67
6	85	76	70	65	84	75	69	65	74	68	64		72	68	64		71	67	64	62
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67	62	59	58
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63	58	55	54
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59	55	51	50
10	69	59	53	49	68	58	53	49	58	52	48		57	52	48		56	51	48	47

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P244440

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBM0H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	84.5	9.2
10°-20°	212.8	23.2
20°-30°	283.9	31.0
30°-40°	218.8	23.9
40°-50°	81.6	8.9
50°-60°	26.7	2.9
60°-70°	6.2	0.7
70°-80°	1.3	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	581.2	63.5
0°-40°	800.0	87.3
0°-60°	908.3	99.2
0°-90°	915.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	915.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	960	
5°	916	85
15°	757	213
25°	625	284
35°	356	219
45°	99	82
55°	28	27
65°	6	6
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P244440

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBM0H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	959.7
1°	955.5
2°	948.6
3°	939.5
4°	928.6
5°	915.5
6°	900.6
7°	883.6
8°	865.4
9°	846.6
10°	829.3
11°	812.6
12°	797.1
13°	782.9
14°	769.8
15°	756.9
16°	743.8
17°	731.0
18°	717.9
19°	705.0
20°	692.6
21°	679.7
22°	667.1
23°	654.0
24°	640.2
25°	625.0
26°	608.0
27°	589.4
28°	568.9
29°	545.9
30°	520.8
32.5°	447.1
35°	356.0
37.5°	263.7
40°	186.6
42.5°	133.7
45°	99.1
47.5°	74.7
50°	55.2
52.5°	39.3
55°	28.0
57.5°	19.3
60°	12.7
62.5°	8.3
65°	5.5



TEST NUMBER: P244440

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBM0H

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	3.7
70°	2.4
72.5°	1.6
75°	1.1
77.5°	0.7
80°	0.4
82.5°	0.2
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)