

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251126

Luminaire Tested: **LSR8B60D010 EC8B609730 8LBW0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251126
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P200903)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B60D010 EC8B609730 8LBW0WH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4744.0 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.11
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251126

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBW0WH

Luminous Intensity Polar Plot





TEST NUMBER: P251126

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBW0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64
6	83	73	67	62	82	73	66	62	71	65	61	69	64	61	68	64	60	59
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54
8	74	63	57	52	73	63	56	52	62	56	52	61	55	51	59	55	51	50
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46
10	66	55	49	45	65	55	49	44	54	48	44	53	48	44	52	48	44	43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P251126

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBW0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	310.5	6.5
10°-20°	955.7	20.1
20°-30°	1402.0	29.6
30°-40°	1238.5	26.1
40°-50°	634.4	13.4
50°-60°	177.4	3.7
60°-70°	22.7	0.5
70°-80°	2.3	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2668.2	56.2
0°-40°	3906.8	82.4
0°-60°	4718.6	99.5
0°-90°	4744.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4744.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3108	
5°	3191	311
15°	3399	956
25°	3092	1402
35°	1992	1239
45°	803	634
55°	181	177
65°	12	23
75°	0	2
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251126

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBW0WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3107.8
2.5°	3119.7
5°	3190.9
7.5°	3288.4
10°	3362.2
12.5°	3398.2
15°	3399.4
17.5°	3365.2
20°	3306.9
22.5°	3214.7
25°	3092.0
27.5°	2908.9
30°	2644.4
32.5°	2330.8
35°	1992.2
37.5°	1662.2
40°	1361.2
42.5°	1077.2
45°	802.6
47.5°	572.8
50°	394.6
52.5°	275.7
55°	181.0
57.5°	114.9
60°	68.6
62.5°	35.6
65°	11.9
67.5°	7.8
70°	6.6
72.5°	3.9
75°	0.0
77.5°	1.1
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251126

CATALOG NUMBER: LSR8B60D010 EC8B609730 8LBW0WH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)