

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246384

Luminaire Tested: **LD8B10D010 ER8B10930 8LBN0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246384
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201749)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10930 8LBN0B
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: 1887 (1 lamp)
Luminaire Lumens: 558.3 lumens
Efficiency: 29.6%
Efficacy: 54.7 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246384

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBN0B

Luminous Intensity Polar Plot





TEST NUMBER: P246384

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBN0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	35	35	35	35	34	34	34	34	33	33	33		31	31	31		30	30	30	30
1	34	33	32	32	33	32	32	31	31	31	30		30	30	29		29	29	28	28
2	32	31	30	29	32	30	29	29	29	29	28		29	28	27		28	27	27	26
3	31	29	28	27	30	29	27	26	28	27	26		27	26	26		26	26	25	25
4	29	27	26	25	29	27	26	24	26	25	24		26	25	24		25	24	24	23
5	28	26	24	23	28	25	24	23	25	24	23		24	23	22		24	23	22	22
6	27	24	23	21	26	24	23	21	24	22	21		23	22	21		23	22	21	21
7	26	23	21	20	25	23	21	20	22	21	20		22	21	20		22	21	20	19
8	24	22	20	19	24	22	20	19	21	20	19		21	20	19		21	20	19	18
9	23	21	19	18	23	21	19	18	20	19	18		20	19	18		20	19	18	17
10	22	20	18	17	22	20	18	17	19	18	17		19	18	17		19	18	17	17

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P246384

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBN0B

ZONAL LUMENS:

CANDELA DISTRIBUTION:

Zone	Lumens	% Fixture	% Lamp	0°	Flux	
0°-10°	79.9	14.3	4.2	0°	891	
10°-20°	174.2	31.2	9.2	5°	874	80
20°-30°	186.7	33.4	9.9	15°	621	174
30°-40°	101.2	18.1	5.4	25°	414	187
40°-50°	15.7	2.8	0.8	35°	158	101
50°-60°	0.5	0.1	0.0	45°	14	16
60°-70°	0.1	0.0	0.0	55°	0	0
70°-80°	0.0	0.0	0.0	65°	0	0
80°-90°	0.0	0.0	0.0	75°	0	0
90°-100°	0.0	0.0	0.0	85°	0	0
100°-110°	0.0	0.0	0.0	90°	0	0
110°-120°	0.0	0.0	0.0	95°	0	0
120°-130°	0.0	0.0	0.0	105°	0	0
130°-140°	0.0	0.0	0.0	115°	0	0
140°-150°	0.0	0.0	0.0	125°	0	0
150°-160°	0.0	0.0	0.0	135°	0	0
160°-170°	0.0	0.0	0.0	145°	0	0
170°-180°	0.0	0.0	0.0	155°	0	0
0°-30°	440.8	79.0	23.4	165°	0	0
0°-40°	542.0	97.1	28.7	175°	0	0
0°-60°	558.2	100.0	29.6	180°	0	0
0°-90°	558.3	100.0	29.6			
90°-120°	0.0	0.0	0.0			
90°-150°	0.0	0.0	0.0			
90°-180°	0.0	0.0	0.0			
0°-180°	558.3	100.0	29.6			



TEST NUMBER: P246384

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBN0B

CANDELA DISTRIBUTION (FULL):

	0°
0°	891.1
2.5°	890.5
5°	873.6
7.5°	832.0
10°	767.2
12.5°	691.9
15°	620.9
17.5°	560.9
20°	508.6
22.5°	461.6
25°	413.8
27.5°	359.7
30°	296.2
32.5°	225.8
35°	158.4
37.5°	101.5
40°	58.5
42.5°	31.3
45°	14.5
47.5°	7.6
50°	2.7
52.5°	0.3
55°	0.0
57.5°	0.3
60°	0.3
62.5°	0.0
65°	0.0
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P246384

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBN0B

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)