

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245376

Luminaire Tested: **LD8B10D010 ER8B10930 8LBS0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245376
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10930 8LBS0WH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1001.0 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245376

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBS0WH

Luminous Intensity Polar Plot





TEST NUMBER: P245376

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBS0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57		66	60	56		64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47		56	51	47		55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43		52	47	43		51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39		49	43	39		48	43	39	38

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P245376

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBS0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.1	5.4
10°-20°	160.4	16.0
20°-30°	248.3	24.8
30°-40°	269.0	26.9
40°-50°	193.6	19.3
50°-60°	64.8	6.5
60°-70°	9.8	1.0
70°-80°	0.9	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	462.9	46.2
0°-40°	731.9	73.1
0°-60°	990.3	98.9
0°-90°	1001.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1001.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	567	
5°	567	54
15°	568	160
25°	542	248
35°	434	269
45°	255	194
55°	66	65
65°	9	10
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P245376

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBS0WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	567.0
2.5°	567.0
5°	567.0
7.5°	567.3
10°	567.6
12.5°	568.1
15°	567.6
17.5°	565.3
20°	560.1
22.5°	552.2
25°	542.3
27.5°	526.8
30°	502.4
32.5°	470.5
35°	433.7
37.5°	394.0
40°	350.9
42.5°	304.5
45°	254.9
47.5°	201.3
50°	149.5
52.5°	102.6
55°	65.5
57.5°	39.1
60°	23.4
62.5°	14.2
65°	8.7
67.5°	4.4
70°	2.0
72.5°	0.9
75°	0.6
77.5°	0.6
80°	0.3
82.5°	0.3
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)