

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251375

Luminaire Tested: **LSR8B70D010 EC8B70830 8LBM0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251375
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201569)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B70D010 EC8B70830 8LBM0B
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4531.0 lumens
Efficiency: N/A
Efficacy: 59.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.87
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251375

CATALOG NUMBER: LSR8B70D010 EC8B70830 8LBM0B

Luminous Intensity Polar Plot





TEST NUMBER: P251375

CATALOG NUMBER: LSR8B70D010 EC8B70830 8LBM0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87
3	103	96	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	181253
5°	175708
10°	153886
15°	135879
20°	124485
25°	114661
30°	95440
35°	63389
40°	30839
45°	11138
50°	3377
55°	231
60°	0
65°	146
70°	0
75°	0
80°	355
85°	0



TEST NUMBER: P251375

CATALOG NUMBER: LSR8B70D010 EC8B70830 8LBM0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	516.6	11.4
10°-20°	1200.9	26.5
20°-30°	1519.9	33.5
30°-40°	1042.7	23.0
40°-50°	237.1	5.2
50°-60°	11.7	0.3
60°-70°	0.5	0.0
70°-80°	0.8	0.0
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3237.4	71.4
0°-40°	4280.1	94.5
0°-60°	4528.9	100.0
0°-90°	4531.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4531.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5878	
5°	5676	517
15°	4256	1201
25°	3370	1520
35°	1684	1043
45°	255	237
55°	4	12
65°	2	0
75°	0	1
85°	0	1
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251375

CATALOG NUMBER: LSR8B70D010 EC8B70830 8LBM0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	5877.9
2.5°	5877.9
5°	5676.4
7.5°	5330.0
10°	4914.6
12.5°	4549.2
15°	4256.3
17.5°	4011.3
20°	3793.5
22.5°	3587.8
25°	3370.0
27.5°	3066.6
30°	2680.4
32.5°	2194.8
35°	1683.9
37.5°	1189.7
40°	766.1
42.5°	450.7
45°	255.4
47.5°	137.0
50°	70.4
52.5°	12.5
55°	4.3
57.5°	2.0
60°	0.0
62.5°	0.0
65°	2.0
67.5°	0.0
70°	0.0
72.5°	2.0
75°	0.0
77.5°	0.0
80°	2.0
82.5°	0.0
85°	0.0
87.5°	2.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251375

CATALOG NUMBER: LSR8B70D010 EC8B70830 8LBM0B

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)