

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244296

Luminaire Tested: **LD8B10D010 ER8B10930 8LBW0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244296
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27940)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10930 8LBW0H
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 936.0 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.12
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244296

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBW0H

Luminous Intensity Polar Plot





TEST NUMBER: P244296

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBW0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	95	93	92
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83	79	77	75
4	93	84	78	73	91	83	77	72	81	75	71		79	74	71		77	73	70	68
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71	67	63	62
6	82	71	65	60	80	71	64	59	69	63	59		68	62	58		66	62	58	56
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		62	57	53	52
8	72	61	54	50	71	61	54	50	60	54	49		58	53	49		57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54	49	45	44
10	64	53	47	42	63	53	47	42	52	46	42		51	46	42		50	45	42	40

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244296

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBW0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.1	6.3
10°-20°	169.7	18.1
20°-30°	255.4	27.3
30°-40°	252.8	27.0
40°-50°	128.5	13.7
50°-60°	51.8	5.5
60°-70°	15.7	1.7
70°-80°	2.7	0.3
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	484.2	51.7
0°-40°	737.1	78.7
0°-60°	917.3	98.0
0°-90°	936.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	936.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	628	
5°	624	59
15°	602	170
25°	558	255
35°	416	253
45°	158	128
55°	56	52
65°	14	16
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P244296

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBW0H

CANDELA DISTRIBUTION (FULL):

	0°
0°	627.6
1°	626.3
2°	625.2
3°	625.0
4°	624.6
5°	623.8
6°	622.8
7°	620.6
8°	617.3
9°	614.4
10°	611.2
11°	608.5
12°	606.6
13°	605.2
14°	603.5
15°	601.6
16°	599.3
17°	596.3
18°	592.8
19°	588.6
20°	584.0
21°	579.2
22°	574.4
23°	569.2
24°	563.8
25°	557.8
26°	551.3
27°	543.0
28°	533.3
29°	521.6
30°	508.0
32.5°	468.6
35°	416.1
37.5°	350.6
40°	277.6
42.5°	209.6
45°	157.5
47.5°	120.4
50°	94.4
52.5°	73.3
55°	55.7
57.5°	41.4
60°	31.2
62.5°	22.2
65°	14.3



TEST NUMBER: P244296

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBW0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	9.0
70°	5.7
72.5°	3.5
75°	2.1
77.5°	1.3
80°	0.8
82.5°	0.6
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)