

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250987

Luminaire Tested: **LSR8B70D010 EC8B70830 8LBS0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250987
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B70D010 EC8B70830 8LBS0H
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7936.0 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250987

CATALOG NUMBER: LSR8B70D010 EC8B70830 8LBS0H

Luminous Intensity Polar Plot





TEST NUMBER: P250987

CATALOG NUMBER: LSR8B70D010 EC8B70830 8LBS0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 102 | 103 | 100 | 98 | | 99 | 97 | 95 | | 95 | 94 | 93 | 91 |
| 2 | 105 | 99 | 94 | 90 | 103 | 97 | 93 | 89 | 94 | 90 | 87 | | 91 | 88 | 85 | | 88 | 85 | 83 | 81 |
| 3 | 98 | 90 | 84 | 79 | 96 | 89 | 83 | 78 | 86 | 81 | 77 | | 83 | 79 | 76 | | 81 | 78 | 75 | 73 |
| 4 | 91 | 82 | 75 | 70 | 89 | 81 | 75 | 70 | 79 | 73 | 69 | | 76 | 72 | 68 | | 74 | 70 | 67 | 65 |
| 5 | 85 | 75 | 68 | 63 | 83 | 74 | 67 | 62 | 72 | 66 | 62 | | 70 | 65 | 61 | | 69 | 64 | 60 | 59 |
| 6 | 80 | 69 | 61 | 56 | 78 | 68 | 61 | 56 | 66 | 60 | 56 | | 65 | 59 | 55 | | 63 | 58 | 55 | 53 |
| 7 | 75 | 63 | 56 | 51 | 73 | 63 | 56 | 51 | 61 | 55 | 50 | | 60 | 54 | 50 | | 59 | 54 | 50 | 48 |
| 8 | 70 | 58 | 51 | 46 | 68 | 58 | 51 | 46 | 57 | 50 | 46 | | 55 | 50 | 46 | | 54 | 49 | 45 | 44 |
| 9 | 66 | 54 | 47 | 42 | 64 | 53 | 47 | 42 | 52 | 46 | 42 | | 51 | 46 | 42 | | 51 | 45 | 42 | 40 |
| 10 | 62 | 50 | 43 | 39 | 61 | 50 | 43 | 39 | 49 | 43 | 38 | | 48 | 42 | 38 | | 47 | 42 | 38 | 37 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 142017 |
| 5° | 141544 |
| 10° | 140469 |
| 15° | 139480 |
| 20° | 138536 |
| 25° | 136712 |
| 30° | 132489 |
| 35° | 125005 |
| 40° | 113609 |
| 45° | 93481 |
| 50° | 62307 |
| 55° | 32461 |
| 60° | 15301 |
| 65° | 8026 |
| 70° | 4012 |
| 75° | 2788 |
| 80° | 2078 |
| 85° | 1663 |



TEST NUMBER: P250987

CATALOG NUMBER: LSR8B70D010 EC8B70830 8LBS0H

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 433.8 | 5.5 |
| 10°-20° | 1233.2 | 15.5 |
| 20°-30° | 1844.7 | 23.2 |
| 30°-40° | 2063.3 | 26.0 |
| 40°-50° | 1618.7 | 20.4 |
| 50°-60° | 590.6 | 7.4 |
| 60°-70° | 120.4 | 1.5 |
| 70°-80° | 25.9 | 0.3 |
| 80°-90° | 5.4 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 3511.6 | 44.2 |
| 0°-40° | 5575.0 | 70.2 |
| 0°-60° | 7784.3 | 98.1 |
| 0°-90° | 7936.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 7936.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 4606 | |
| 5° | 4573 | 434 |
| 15° | 4369 | 1233 |
| 25° | 4018 | 1845 |
| 35° | 3321 | 2063 |
| 45° | 2144 | 1619 |
| 55° | 604 | 591 |
| 65° | 110 | 120 |
| 75° | 23 | 26 |
| 85° | 5 | 5 |
| 90° | 0 | |



TEST NUMBER: P250987

CATALOG NUMBER: LSR8B70D010 EC8B70830 8LBS0H

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 4605.5 |
| 2.5° | 4598.5 |
| 5° | 4572.7 |
| 7.5° | 4535.3 |
| 10° | 4486.1 |
| 12.5° | 4430.0 |
| 15° | 4369.1 |
| 17.5° | 4301.3 |
| 20° | 4221.7 |
| 22.5° | 4128.1 |
| 25° | 4018.1 |
| 27.5° | 3882.4 |
| 30° | 3720.9 |
| 32.5° | 3531.3 |
| 35° | 3320.7 |
| 37.5° | 3084.4 |
| 40° | 2822.3 |
| 42.5° | 2511.0 |
| 45° | 2143.6 |
| 47.5° | 1729.4 |
| 50° | 1298.8 |
| 52.5° | 910.3 |
| 55° | 603.8 |
| 57.5° | 386.1 |
| 60° | 248.1 |
| 62.5° | 163.8 |
| 65° | 110.0 |
| 67.5° | 70.2 |
| 70° | 44.5 |
| 72.5° | 30.4 |
| 75° | 23.4 |
| 77.5° | 16.4 |
| 80° | 11.7 |
| 82.5° | 7.0 |
| 85° | 4.7 |
| 87.5° | 2.3 |
| 90° | 0.0 |

(END OF REPORT)