

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245352

Luminaire Tested: **LD8B10D010 ER8B10935 8LBS0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245352
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10935 8LBS0WH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 3500 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1034.0 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245352

CATALOG NUMBER: LD8B10D010 ER8B10935 8LBS0WH

Luminous Intensity Polar Plot





TEST NUMBER: P245352

CATALOG NUMBER: LD8B10D010 ER8B10935 8LBS0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57		66	60	56		64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47		56	51	47		55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43		52	47	43		51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39		49	43	39		48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	18061
5°	18130
10°	18358
15°	18717
20°	18984
25°	19060
30°	18476
35°	16865
40°	14588
45°	11487
50°	7407
55°	3634
60°	1492
65°	657
70°	189
75°	71
80°	53
85°	0



TEST NUMBER: P245352

CATALOG NUMBER: LD8B10D010 ER8B10935 8LBS0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.9	5.4
10°-20°	165.7	16.0
20°-30°	256.5	24.8
30°-40°	277.9	26.9
40°-50°	200.0	19.3
50°-60°	66.9	6.5
60°-70°	10.1	1.0
70°-80°	0.9	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	478.1	46.2
0°-40°	756.0	73.1
0°-60°	1022.9	98.9
0°-90°	1034.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1034.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	586	
5°	586	56
15°	586	166
25°	560	257
35°	448	278
45°	263	200
55°	68	67
65°	9	10
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P245352

CATALOG NUMBER: LD8B10D010 ER8B10935 8LBS0WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	585.7
2.5°	585.7
5°	585.7
7.5°	586.0
10°	586.3
12.5°	586.9
15°	586.3
17.5°	583.9
20°	578.5
22.5°	570.4
25°	560.2
27.5°	544.1
30°	518.9
32.5°	486.0
35°	448.0
37.5°	407.0
40°	362.4
42.5°	314.5
45°	263.4
47.5°	208.0
50°	154.4
52.5°	105.9
55°	67.6
57.5°	40.4
60°	24.2
62.5°	14.7
65°	9.0
67.5°	4.5
70°	2.1
72.5°	0.9
75°	0.6
77.5°	0.6
80°	0.3
82.5°	0.3
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)