

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244704

Luminaire Tested: **LD8B10D010 ER8B10935 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244704
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10935 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 3500 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 940.0 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244704

CATALOG NUMBER: LD8B10D010 ER8B10935 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244704

CATALOG NUMBER: LD8B10D010 ER8B10935 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	21006
5°	20584
10°	19933
15°	19662
20°	19545
25°	19298
30°	18263
35°	15061
40°	9403
45°	6049
50°	4692
55°	3613
60°	2738
65°	1780
70°	757
75°	369
80°	160
85°	106



TEST NUMBER: P244704

CATALOG NUMBER: LD8B10D010 ER8B10935 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.5	6.7
10°-20°	174.0	18.5
20°-30°	259.2	27.6
30°-40°	240.7	25.6
40°-50°	113.7	12.1
50°-60°	61.1	6.5
60°-70°	24.6	2.6
70°-80°	3.8	0.4
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	495.8	52.7
0°-40°	736.5	78.3
0°-60°	911.3	96.9
0°-90°	940.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	940.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	681	
5°	665	63
15°	616	174
25°	567	259
35°	400	241
45°	139	114
55°	67	61
65°	24	25
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P244704

CATALOG NUMBER: LD8B10D010 ER8B10935 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	681.2
2.5°	676.5
5°	665.0
7.5°	650.3
10°	636.6
12.5°	625.3
15°	615.9
17.5°	606.3
20°	595.6
22.5°	583.5
25°	567.2
27.5°	544.4
30°	512.9
32.5°	466.6
35°	400.1
37.5°	315.2
40°	233.6
42.5°	174.0
45°	138.7
47.5°	115.9
50°	97.8
52.5°	81.5
55°	67.2
57.5°	54.7
60°	44.4
62.5°	34.7
65°	24.4
67.5°	14.4
70°	8.4
72.5°	5.0
75°	3.1
77.5°	1.9
80°	0.9
82.5°	0.6
85°	0.3
87.5°	0.0
90°	0.0

(END OF REPORT)