

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251225

Luminaire Tested: **LSR8B70D010 EC8B70840 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251225
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B70D010 EC8B70840 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 4000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6698.0 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251225

CATALOG NUMBER: LSR8B70D010 EC8B70840 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P251225

CATALOG NUMBER: LSR8B70D010 EC8B70840 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66	74	70	66	73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61	69	64	60	68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51	60	55	51	59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	160824
5°	157021
10°	152101
15°	149903
20°	148135
25°	144953
30°	135768
35°	110862
40°	66186
45°	39750
50°	28649
55°	19499
60°	12230
65°	5998
70°	1524
75°	572
80°	426
85°	0



TEST NUMBER: P251225

CATALOG NUMBER: LSR8B70D010 EC8B70840 8LBW0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	477.2	7.1
10°-20°	1325.1	19.8
20°-30°	1945.9	29.1
30°-40°	1764.0	26.3
40°-50°	755.1	11.3
50°-60°	334.1	5.0
60°-70°	89.1	1.3
70°-80°	7.0	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3748.3	56.0
0°-40°	5512.3	82.3
0°-60°	6601.6	98.6
0°-90°	6698.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6698.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5215	
5°	5073	477
15°	4696	1325
25°	4260	1946
35°	2945	1764
45°	912	755
55°	363	334
65°	82	89
75°	5	7
85°	0	0
90°	0	



TEST NUMBER: P251225

CATALOG NUMBER: LSR8B70D010 EC8B70840 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	5215.4
2.5°	5174.3
5°	5072.7
7.5°	4956.7
10°	4857.6
12.5°	4775.3
15°	4695.6
17.5°	4610.9
20°	4514.2
22.5°	4400.6
25°	4260.3
27.5°	4071.7
30°	3813.0
32.5°	3450.3
35°	2945.0
37.5°	2282.5
40°	1644.2
42.5°	1187.2
45°	911.5
47.5°	735.0
50°	597.2
52.5°	473.9
55°	362.7
57.5°	270.8
60°	198.3
62.5°	137.8
65°	82.2
67.5°	36.3
70°	16.9
72.5°	9.7
75°	4.8
77.5°	2.4
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)