

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251065

Luminaire Tested: **LSR8B70D010 EC8B70850 8LBM0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251065  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201704)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B70D010 EC8B70850 8LBM0WMH  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 5000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7293.0 lumens  
Efficiency: N/A  
Efficacy: 96.1 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 75.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251065

CATALOG NUMBER: LSR8B70D010 EC8B70850 8LBM0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P251065

CATALOG NUMBER: LSR8B70D010 EC8B70850 8LBM0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	73		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	75	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67	63	60	59
9	77	67	61	58	76	67	61	57	66	61	57		65	60	57		64	60	57	56
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	282313
5°	287734
10°	274334
15°	242234
20°	209916
25°	177374
30°	133297
35°	89251
40°	49979
45°	20078
50°	6951
55°	1925
60°	1092
65°	949
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P251065

CATALOG NUMBER: LSR8B70D010 EC8B70850 8LBM0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	869.7	11.9
10°-20°	2116.4	29.0
20°-30°	2348.6	32.2
30°-40°	1487.9	20.4
40°-50°	412.9	5.7
50°-60°	47.3	0.6
60°-70°	9.3	0.1
70°-80°	1.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5334.7	73.1
0°-40°	6822.6	93.6
0°-60°	7282.7	99.9
0°-90°	7293.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7293.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9155	
5°	9296	870
15°	7588	2116
25°	5213	2349
35°	2371	1488
45°	460	413
55°	36	47
65°	13	9
75°	0	1
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251065

CATALOG NUMBER: LSR8B70D010 EC8B70850 8LBM0WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	9155.2
2.5°	9222.9
5°	9295.5
7.5°	9150.5
10°	8761.3
12.5°	8206.2
15°	7587.8
17.5°	6980.6
20°	6396.9
22.5°	5824.1
25°	5213.2
27.5°	4498.7
30°	3743.6
32.5°	3012.1
35°	2370.9
37.5°	1791.6
40°	1241.6
42.5°	772.2
45°	460.4
47.5°	264.8
50°	144.9
52.5°	71.0
55°	35.8
57.5°	27.0
60°	17.7
62.5°	9.3
65°	13.0
67.5°	6.5
70°	0.0
72.5°	1.9
75°	0.0
77.5°	1.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251065

CATALOG NUMBER: LSR8B70D010 EC8B70850 8LBM0WMH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)