

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250873

Luminaire Tested: **LSR8B70D010 EC8B70850 8LBSOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250873
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B70D010 EC8B70850 8LBS0LI
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 5000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8596.0 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250873

CATALOG NUMBER: LSR8B70D010 EC8B70850 8LBS0LI

Luminous Intensity Polar Plot





TEST NUMBER: P250873

CATALOG NUMBER: LSR8B70D010 EC8B70850 8LBSOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	105	99	95	91	103	98	93	90	94	91	88	91	88	86	88	86	84	82				82
3	98	91	85	80	96	89	84	79	86	82	78	84	80	77	82	78	75	74				74
4	92	83	76	71	90	82	75	71	79	74	70	77	73	69	75	71	68	66				66
5	86	76	69	63	84	75	68	63	73	67	63	71	66	62	69	65	61	60				60
6	80	70	62	57	79	69	62	57	67	61	56	66	60	56	64	59	56	54				54
7	75	64	57	52	74	63	56	52	62	56	51	61	55	51	59	54	51	49				49
8	71	59	52	47	69	58	52	47	57	51	47	56	51	46	55	50	46	45				45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41				41
10	62	51	44	39	61	50	44	39	50	43	39	49	43	39	48	43	39	37				37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	147789
5°	148431
10°	150842
15°	154656
20°	157356
25°	157532
30°	152657
35°	139769
40°	121474
45°	96119
50°	62331
55°	31149
60°	13075
65°	5757
70°	1776
75°	882
80°	870
85°	885



TEST NUMBER: P250873

CATALOG NUMBER: LSR8B70D010 EC8B70850 8LBS0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	458.4	5.3
10°-20°	1369.0	15.9
20°-30°	2120.7	24.7
30°-40°	2303.1	26.8
40°-50°	1673.6	19.5
50°-60°	568.8	6.6
60°-70°	90.6	1.1
70°-80°	9.7	0.1
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3948.1	45.9
0°-40°	6251.2	72.7
0°-60°	8493.7	98.8
0°-90°	8596.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8596.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4793	
5°	4795	458
15°	4844	1369
25°	4630	2121
35°	3713	2303
45°	2204	1674
55°	579	569
65°	79	91
75°	7	10
85°	2	2
90°	0	



TEST NUMBER: P250873

CATALOG NUMBER: LSR8B70D010 EC8B70850 8LBS0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4792.7
2.5°	4792.7
5°	4795.2
7.5°	4802.6
10°	4817.4
12.5°	4834.7
15°	4844.5
17.5°	4834.7
20°	4795.2
22.5°	4723.7
25°	4630.0
27.5°	4489.5
30°	4287.3
32.5°	4018.6
35°	3712.9
37.5°	3380.1
40°	3017.7
42.5°	2625.7
45°	2204.1
47.5°	1750.4
50°	1299.3
52.5°	890.0
55°	579.4
57.5°	352.6
60°	212.0
62.5°	130.7
65°	78.9
67.5°	44.4
70°	19.7
72.5°	12.3
75°	7.4
77.5°	4.9
80°	4.9
82.5°	2.5
85°	2.5
87.5°	0.0
90°	0.0

(END OF REPORT)