

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243846

Luminaire Tested: **LD8B10D010 ER8B10940 8LBWOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243846
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10940 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 4000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1070.0 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243846

CATALOG NUMBER: LD8B10D010 ER8B10940 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243846

CATALOG NUMBER: LD8B10D010 ER8B10940 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	18983
5°	19548
10°	21173
15°	23167
20°	24103
25°	24014
30°	22525
35°	18890
40°	13151
45°	7531
50°	4044
55°	1667
60°	413
65°	109
70°	54
75°	36
80°	53
85°	0



TEST NUMBER: P243846

CATALOG NUMBER: LD8B10D010 ER8B10940 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.7	5.8
10°-20°	204.5	19.1
20°-30°	321.8	30.1
30°-40°	306.1	28.6
40°-50°	141.1	13.2
50°-60°	32.1	3.0
60°-70°	2.1	0.2
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	588.1	55.0
0°-40°	894.2	83.6
0°-60°	1067.4	99.8
0°-90°	1070.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1070.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	616	
5°	632	62
15°	726	205
25°	706	322
35°	502	306
45°	173	141
55°	31	32
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P243846

CATALOG NUMBER: LD8B10D010 ER8B10940 8LBW0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	615.6
1°	615.4
2°	616.5
3°	620.0
4°	625.3
5°	631.5
6°	639.1
7°	647.3
8°	655.8
9°	665.7
10°	676.2
11°	686.8
12°	697.9
13°	708.4
14°	718.1
15°	725.7
16°	731.3
17°	735.1
18°	736.8
19°	736.5
20°	734.5
21°	731.0
22°	726.6
23°	720.7
24°	714.0
25°	705.8
26°	696.1
27°	683.9
28°	669.2
29°	652.2
30°	632.6
32.5°	573.8
35°	501.8
37.5°	418.0
40°	326.7
42.5°	241.5
45°	172.7
47.5°	122.4
50°	84.3
52.5°	53.9
55°	31.0
57.5°	15.5
60°	6.7
62.5°	2.6
65°	1.5



TEST NUMBER: P243846

CATALOG NUMBER: LD8B10D010 ER8B10940 8LBW0LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.9
70°	0.6
72.5°	0.6
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)