

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246582

Luminaire Tested: **LD8B10D010 ER8B10940 8LBW0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246582
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-48)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10940 8LBW0MW
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 4000 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1030.0 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246582

CATALOG NUMBER: LD8B10D010 ER8B10940 8LBW0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246582

CATALOG NUMBER: LD8B10D010 ER8B10940 8LBW0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	86	83	80	78
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62
5	84	73	66	60	82	72	65	60	70	64	59	68	63	59	67	62	58	56
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47
8	69	58	50	45	68	57	50	45	56	50	45	55	49	45	54	48	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	40
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	21043
5°	20690
10°	20040
15°	19576
20°	19295
25°	18917
30°	17761
35°	14501
40°	8981
45°	6083
50°	5359
55°	5059
60°	5014
65°	4859
70°	4355
75°	3777
80°	3196
85°	2547



TEST NUMBER: P246582

CATALOG NUMBER: LD8B10D010 ER8B10940 8LBW0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.9	6.1
10°-20°	173.2	16.8
20°-30°	254.0	24.7
30°-40°	232.2	22.5
40°-50°	114.9	11.2
50°-60°	85.0	8.3
60°-70°	65.3	6.3
70°-80°	34.1	3.3
80°-90°	8.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	490.0	47.6
0°-40°	722.2	70.1
0°-60°	922.1	89.5
0°-90°	1030.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1030.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	682	
5°	668	63
15°	613	173
25°	556	254
35°	385	232
45°	140	115
55°	94	85
65°	67	65
75°	32	34
85°	7	8
90°	0	



TEST NUMBER: P246582

CATALOG NUMBER: LD8B10D010 ER8B10940 8LBW0MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	682.4
2.5°	678.9
5°	668.4
7.5°	654.4
10°	640.0
12.5°	625.9
15°	613.2
17.5°	601.1
20°	588.0
22.5°	573.3
25°	556.0
27.5°	532.2
30°	498.8
32.5°	452.1
35°	385.2
37.5°	302.2
40°	223.1
42.5°	168.9
45°	139.5
47.5°	123.5
50°	111.7
52.5°	102.3
55°	94.1
57.5°	87.2
60°	81.3
62.5°	75.1
65°	66.6
67.5°	57.5
70°	48.3
72.5°	39.9
75°	31.7
77.5°	24.5
80°	18.0
82.5°	12.4
85°	7.2
87.5°	2.6
90°	0.0

(END OF REPORT)