

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251023

Luminaire Tested: **LSR8B70D010 EC8B70935 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251023
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B70D010 EC8B70935 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 3500 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6245.0 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251023

CATALOG NUMBER: LSR8B70D010 EC8B70935 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P251023

CATALOG NUMBER: LSR8B70D010 EC8B70935 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	139559
5°	136752
10°	132422
15°	130637
20°	129857
25°	128216
30°	121323
35°	100066
40°	62482
45°	40177
50°	31158
55°	23983
60°	18175
65°	11813
70°	5049
75°	2478
80°	1101
85°	743



TEST NUMBER: P251023

CATALOG NUMBER: LSR8B70D010 EC8B70935 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	415.5	6.7
10°-20°	1156.1	18.5
20°-30°	1722.0	27.6
30°-40°	1599.2	25.6
40°-50°	755.3	12.1
50°-60°	405.8	6.5
60°-70°	163.0	2.6
70°-80°	25.6	0.4
80°-90°	2.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3293.6	52.7
0°-40°	4892.8	78.3
0°-60°	6053.9	96.9
0°-90°	6245.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6245.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4526	
5°	4418	416
15°	4092	1156
25°	3768	1722
35°	2658	1599
45°	921	755
55°	446	406
65°	162	163
75°	21	26
85°	2	3
90°	0	



TEST NUMBER: P251023

CATALOG NUMBER: LSR8B70D010 EC8B70935 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4525.8
2.5°	4494.7
5°	4417.9
7.5°	4320.4
10°	4229.1
12.5°	4154.3
15°	4092.1
17.5°	4027.8
20°	3957.2
22.5°	3876.3
25°	3768.4
27.5°	3616.9
30°	3407.3
32.5°	3100.2
35°	2658.2
37.5°	2093.8
40°	1552.2
42.5°	1155.8
45°	921.3
47.5°	769.9
50°	649.5
52.5°	541.6
55°	446.1
57.5°	363.1
60°	294.7
62.5°	230.3
65°	161.9
67.5°	95.5
70°	56.0
72.5°	33.2
75°	20.8
77.5°	12.5
80°	6.2
82.5°	4.2
85°	2.1
87.5°	0.0
90°	0.0

(END OF REPORT)