

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251187

Luminaire Tested: **LSR8B70D010 EC8B709730 8LBS0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251187
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B70D010 EC8B709730 8LBS0WH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 3000 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6948.0 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251187

CATALOG NUMBER: LSR8B70D010 EC8B709730 8LBS0WH

Luminous Intensity Polar Plot





TEST NUMBER: P251187

CATALOG NUMBER: LSR8B70D010 EC8B709730 8LBS0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121353
5°	121817
10°	123354
15°	125765
20°	127560
25°	128084
30°	124161
35°	113324
40°	98030
45°	77171
50°	49781
55°	24435
60°	10046
65°	4400
70°	1271
75°	477
80°	355
85°	0



TEST NUMBER: P251187

CATALOG NUMBER: LSR8B70D010 EC8B709730 8LBS0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	375.8	5.4
10°-20°	1113.3	16.0
20°-30°	1723.7	24.8
30°-40°	1867.3	26.9
40°-50°	1343.7	19.3
50°-60°	449.6	6.5
60°-70°	67.9	1.0
70°-80°	5.8	0.1
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3212.8	46.2
0°-40°	5080.1	73.1
0°-60°	6873.5	98.9
0°-90°	6948.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6948.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3935	
5°	3935	376
15°	3940	1113
25°	3764	1724
35°	3010	1867
45°	1770	1344
55°	454	450
65°	60	68
75°	4	6
85°	0	1
90°	0	



TEST NUMBER: P251187

CATALOG NUMBER: LSR8B70D010 EC8B709730 8LBS0WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3935.4
2.5°	3935.4
5°	3935.4
7.5°	3937.4
10°	3939.5
12.5°	3943.5
15°	3939.5
17.5°	3923.4
20°	3887.2
22.5°	3832.9
25°	3764.5
27.5°	3655.9
30°	3487.0
32.5°	3265.8
35°	3010.4
37.5°	2734.9
40°	2435.3
42.5°	2113.5
45°	1769.6
47.5°	1397.6
50°	1037.7
52.5°	711.9
55°	454.5
57.5°	271.5
60°	162.9
62.5°	98.5
65°	60.3
67.5°	30.2
70°	14.1
72.5°	6.0
75°	4.0
77.5°	4.0
80°	2.0
82.5°	2.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)