

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250477

Luminaire Tested: **LSR8B80D010 EC8B80840 8LBM0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250477  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14005)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B80D010 EC8B80840 8LBM0GPH  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 4000 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7277.1 lumens  
Efficiency: N/A  
Efficacy: 97.8 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 74.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250477

CATALOG NUMBER: LSR8B80D010 EC8B80840 8LBM0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P250477

CATALOG NUMBER: LSR8B80D010 EC8B80840 8LBM0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	284591
5°	277398
10°	248674
15°	221477
20°	202044
25°	183567
30°	150524
35°	99061
40°	49416
45°	18394
50°	5589
55°	677
60°	389
65°	0
70°	289
75°	1132
80°	0
85°	1132



TEST NUMBER: P250477

CATALOG NUMBER: LSR8B80D010 EC8B80840 8LBM0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	821.7	11.3
10°-20°	1953.6	26.8
20°-30°	2433.8	33.4
30°-40°	1641.7	22.6
40°-50°	388.2	5.3
50°-60°	28.4	0.4
60°-70°	5.1	0.1
70°-80°	3.8	0.1
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5209.1	71.6
0°-40°	6850.8	94.1
0°-60°	7267.4	99.9
0°-90°	7277.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7277.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9229	
5°	8962	822
15°	6938	1954
25°	5395	2434
35°	2632	1642
45°	422	388
55°	13	28
65°	0	5
75°	10	4
85°	3	1
90°	0	



TEST NUMBER: P250477

CATALOG NUMBER: LSR8B80D010 EC8B80840 8LBM0GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9229.1
2.5°	9213.4
5°	8961.6
7.5°	8505.2
10°	7941.8
12.5°	7409.8
15°	6937.6
17.5°	6531.5
20°	6157.0
22.5°	5798.1
25°	5395.2
27.5°	4869.6
30°	4227.4
32.5°	3450.0
35°	2631.5
37.5°	1882.4
40°	1227.6
42.5°	733.5
45°	421.8
47.5°	236.1
50°	116.5
52.5°	53.5
55°	12.6
57.5°	3.2
60°	6.3
62.5°	9.5
65°	0.0
67.5°	6.3
70°	3.2
72.5°	3.2
75°	9.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	3.2
87.5°	0.0
90°	0.0

(END OF REPORT)