

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250400

Luminaire Tested: **LSR8B80D010 EC8B80850 8LBN0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250400  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B80D010 EC8B80850 8LBN0B  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 5000 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5006.1 lumens  
Efficiency: N/A  
Efficacy: 67.3 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 74.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250400

CATALOG NUMBER: LSR8B80D010 EC8B80850 8LBN0B

### Luminous Intensity Polar Plot





TEST NUMBER: P250400

CATALOG NUMBER: LSR8B80D010 EC8B80850 8LBN0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		79	75	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	246663
5°	242720
10°	215652
15°	177894
20°	149822
25°	126369
30°	94618
35°	53545
40°	21174
45°	5682
50°	1089
55°	0
60°	160
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P250400

CATALOG NUMBER: LSR8B80D010 EC8B80850 8LBN0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	718.1	14.3
10°-20°	1560.7	31.2
20°-30°	1675.5	33.5
30°-40°	905.6	18.1
40°-50°	141.3	2.8
50°-60°	3.9	0.1
60°-70°	1.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3954.3	79.0
0°-40°	4859.9	97.1
0°-60°	5005.1	100.0
0°-90°	5006.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5006.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7999	
5°	7841	718
15°	5572	1561
25°	3714	1676
35°	1422	906
45°	130	141
55°	0	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250400

CATALOG NUMBER: LSR8B80D010 EC8B80850 8LBN0B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7999.1
1°	8014.3
2°	8006.7
3°	7979.3
4°	7926.7
5°	7841.3
6°	7723.9
7°	7565.8
8°	7368.0
9°	7140.4
10°	6887.2
11°	6621.7
12°	6346.2
13°	6071.0
14°	5815.3
15°	5572.4
16°	5349.5
17°	5134.1
18°	4933.7
19°	4746.1
20°	4565.6
21°	4390.3
22°	4224.8
23°	4059.8
24°	3887.0
25°	3714.1
26°	3538.7
27°	3338.5
28°	3117.9
29°	2892.8
30°	2657.3
31°	2404.4
32°	2151.2
33°	1900.8
34°	1647.9
35°	1422.4
37.5°	909.1
40°	526.0
42.5°	280.6
45°	130.3
47.5°	70.3
50°	22.7
52.5°	2.6
55°	0.0
57.5°	2.6



TEST NUMBER: P250400

CATALOG NUMBER: LSR8B80D010 EC8B80850 8LBN0B

**CANDELA DISTRIBUTION (continued):**

	0°
60°	2.6
62.5°	0.0
65°	0.0
67.5°	2.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)