

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250617

Luminaire Tested: **LSR8B80D010 EC8B80930 8LBM0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250617
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13928)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B80D010 EC8B80930 8LBM0B
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4406.6 lumens
Efficiency: N/A
Efficacy: 59.2 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250617

CATALOG NUMBER: LSR8B80D010 EC8B80930 8LBM0B

Luminous Intensity Polar Plot





TEST NUMBER: P250617

CATALOG NUMBER: LSR8B80D010 EC8B80930 8LBM0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	74	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	60	58
9	76	66	61	57	75	66	60	57	65	60	56		64	60	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250617

CATALOG NUMBER: LSR8B80D010 EC8B80930 8LBM0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	502.2	11.4
10°-20°	1166.3	26.5
20°-30°	1479.7	33.6
30°-40°	1013.7	23.0
40°-50°	231.0	5.2
50°-60°	11.5	0.3
60°-70°	0.5	0.0
70°-80°	0.8	0.0
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3148.2	71.4
0°-40°	4161.9	94.4
0°-60°	4404.4	99.9
0°-90°	4406.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4406.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5718	
5°	5522	502
15°	4140	1166
25°	3277	1480
35°	1638	1014
45°	249	231
55°	4	12
65°	2	1
75°	0	1
85°	0	1
90°	0	



TEST NUMBER: P250617

CATALOG NUMBER: LSR8B80D010 EC8B80930 8LBM0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	5717.8
1°	5747.6
2°	5736.9
3°	5694.3
4°	5621.9
5°	5521.8
6°	5400.4
7°	5260.0
8°	5104.5
9°	4938.3
10°	4780.7
11°	4636.0
12°	4480.5
13°	4367.6
14°	4248.4
15°	4139.9
16°	4041.9
17°	3945.9
18°	3856.6
19°	3769.3
20°	3690.4
21°	3609.5
22°	3526.4
23°	3454.1
24°	3373.2
25°	3277.4
26°	3170.9
27°	3047.3
28°	2915.3
29°	2768.4
30°	2606.5
31°	2423.4
32°	2233.9
33°	2035.8
34°	1833.5
35°	1637.6
37.5°	1156.3
40°	745.4
42.5°	438.6
45°	249.2
47.5°	134.2
50°	68.2
52.5°	12.8
55°	4.3
57.5°	2.1



TEST NUMBER: P250617

CATALOG NUMBER: LSR8B80D010 EC8B80930 8LBM0B

CANDELA DISTRIBUTION (continued):

	0°
60°	0.0
62.5°	0.0
65°	2.1
67.5°	0.0
70°	0.0
72.5°	2.1
75°	0.0
77.5°	0.0
80°	2.1
82.5°	0.0
85°	0.0
87.5°	2.1
90°	0.0

(END OF REPORT)