

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244944

Luminaire Tested: **LD8B10D010 ER8B109730 8LBS0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244944
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B109730 8LBS0WMH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 893.0 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244944

CATALOG NUMBER: LD8B10D010 ER8B109730 8LBS0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244944

CATALOG NUMBER: LD8B10D010 ER8B109730 8LBS0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55	64	58	54	63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244944

CATALOG NUMBER: LD8B10D010 ER8B109730 8LBS0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.7	5.3
10°-20°	134.9	15.1
20°-30°	200.9	22.5
30°-40°	228.2	25.6
40°-50°	186.5	20.9
50°-60°	73.1	8.2
60°-70°	17.0	1.9
70°-80°	4.1	0.5
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	383.4	42.9
0°-40°	611.6	68.5
0°-60°	871.2	97.6
0°-90°	893.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	893.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	506	
5°	503	48
15°	478	135
25°	437	201
35°	367	228
45°	248	187
55°	76	73
65°	16	17
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P244944

CATALOG NUMBER: LD8B10D010 ER8B109730 8LBS0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	506.3
2.5°	505.5
5°	502.8
7.5°	498.3
10°	492.6
12.5°	485.6
15°	478.4
17.5°	469.8
20°	460.4
22.5°	449.4
25°	437.0
27.5°	422.5
30°	406.1
32.5°	387.6
35°	366.6
37.5°	343.5
40°	317.8
42.5°	286.6
45°	247.7
47.5°	202.0
50°	154.4
52.5°	110.9
55°	76.0
57.5°	49.7
60°	33.3
62.5°	22.8
65°	15.8
67.5°	10.5
70°	7.0
72.5°	4.8
75°	3.8
77.5°	2.7
80°	1.6
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)