

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P249945

Luminaire Tested: **LSR8B80D010 EC8B80930 8LBM0H**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P249945  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13954)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B80D010 EC8B80930 8LBM0H  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6720.4 lumens  
Efficiency: N/A  
Efficacy: 90.3 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 74.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P249945

CATALOG NUMBER: LSR8B80D010 EC8B80930 8LBM0H

### Luminous Intensity Polar Plot






TEST NUMBER: P249945

CATALOG NUMBER: LSR8B80D010 EC8B80930 8LBM0H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97	96	95	93
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91	89	87	86
3	101	95	90	85	99	93	89	85	91	87	83		88	85	82		86	83	81	79
4	96	88	82	78	94	87	82	77	85	80	76		83	79	76		81	77	75	73
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76	72	69	68
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		71	67	64	63
7	81	72	65	61	80	71	65	61	70	64	60		68	64	60		67	63	60	58
8	77	67	61	57	76	67	61	56	65	60	56		64	60	56		63	59	56	54
9	73	63	57	53	72	63	57	53	62	56	53		61	56	52		60	55	52	51
10	70	60	53	49	69	59	53	49	58	53	49		57	53	49		57	52	49	48

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P249945

CATALOG NUMBER: LSR8B80D010 EC8B80930 8LBM0H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	641.3	9.5
10°-20°	1613.4	24.0
20°-30°	2094.6	31.2
30°-40°	1581.0	23.5
40°-50°	578.5	8.6
50°-60°	161.7	2.4
60°-70°	42.5	0.6
70°-80°	7.1	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4349.3	64.7
0°-40°	5930.3	88.2
0°-60°	6670.5	99.3
0°-90°	6720.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6720.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7034	
5°	6904	641
15°	5735	1613
25°	4630	2095
35°	2553	1581
45°	694	578
55°	166	162
65°	40	42
75°	6	7
85°	0	0
90°	0	



TEST NUMBER: P249945

CATALOG NUMBER: LSR8B80D010 EC8B80930 8LBM0H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7034.1
1°	7044.6
2°	7036.2
3°	7008.9
4°	6962.9
5°	6904.1
6°	6818.3
7°	6723.9
8°	6614.9
9°	6495.4
10°	6369.6
11°	6244.0
12°	6113.9
13°	5981.9
14°	5856.1
15°	5734.6
16°	5619.3
17°	5508.3
18°	5407.6
19°	5302.8
20°	5195.9
22.5°	4929.7
25°	4630.1
27.5°	4233.9
30°	3751.8
32.5°	3171.2
35°	2552.9
37.5°	1949.3
40°	1406.4
42.5°	995.6
45°	693.8
47.5°	488.3
50°	329.0
52.5°	241.0
55°	165.6
57.5°	119.5
60°	79.7
62.5°	58.7
65°	39.8
67.5°	27.2
70°	14.7
72.5°	10.4
75°	6.3
77.5°	2.1
80°	2.1



TEST NUMBER: P249945

CATALOG NUMBER: LSR8B80D010 EC8B80930 8LBM0H

**CANDELA DISTRIBUTION (continued):**

	0°
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)