

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250449

Luminaire Tested: **LSR8B80D010 EC8B80930 8LBN0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250449
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B80D010 EC8B80930 8LBN0B
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4081.6 lumens
Efficiency: N/A
Efficacy: 54.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250449

CATALOG NUMBER: LSR8B80D010 EC8B80930 8LBN0B

Luminous Intensity Polar Plot





TEST NUMBER: P250449

CATALOG NUMBER: LSR8B80D010 EC8B80930 8LBN0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		79	75	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250449

CATALOG NUMBER: LSR8B80D010 EC8B80930 8LBN0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	585.5	14.3
10°-20°	1272.5	31.2
20°-30°	1366.1	33.5
30°-40°	738.4	18.1
40°-50°	115.2	2.8
50°-60°	3.2	0.1
60°-70°	0.8	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3224.1	79.0
0°-40°	3962.4	97.1
0°-60°	4080.8	100.0
0°-90°	4081.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4081.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6522	
5°	6393	585
15°	4543	1272
25°	3028	1366
35°	1160	738
45°	106	115
55°	0	3
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250449

CATALOG NUMBER: LSR8B80D010 EC8B80930 8LBN0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	6522.0
1°	6534.3
2°	6528.1
3°	6505.8
4°	6462.9
5°	6393.3
6°	6297.6
7°	6168.6
8°	6007.4
9°	5821.8
10°	5615.4
11°	5398.8
12°	5174.3
13°	4949.9
14°	4741.4
15°	4543.4
16°	4361.6
17°	4185.9
18°	4022.6
19°	3869.7
20°	3722.5
21°	3579.6
22°	3444.6
23°	3310.1
24°	3169.2
25°	3028.2
26°	2885.2
27°	2721.9
28°	2542.2
29°	2358.6
30°	2166.6
31°	1960.4
32°	1753.9
33°	1549.8
34°	1343.6
35°	1159.8
37.5°	741.2
40°	428.9
42.5°	228.8
45°	106.3
47.5°	57.3
50°	18.5
52.5°	2.1
55°	0.0
57.5°	2.1



TEST NUMBER: P250449

CATALOG NUMBER: LSR8B80D010 EC8B80930 8LBN0B

CANDELA DISTRIBUTION (continued):

	0°
60°	2.1
62.5°	0.0
65°	0.0
67.5°	2.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)