

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250626

Luminaire Tested: **LD8B100D010 ER8B100827 8LBN0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250626
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P131425)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B100D010 ER8B100827 8LBN0MW
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 2700 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9432.0 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 106.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250626

CATALOG NUMBER: LD8B100D010 ER8B100827 8LBN0MW

Luminous Intensity Polar Plot





TEST NUMBER: P250626

CATALOG NUMBER: LD8B100D010 ER8B100827 8LBN0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67
5	87	78	71	66	85	77	70	65	75	69	65	73	68	64	71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	57
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	305138
5°	302948
10°	276015
15°	236641
20°	209667
25°	187082
30°	151094
35°	104911
40°	66512
45°	49348
50°	42158
55°	37052
60°	33038
65°	29646
70°	25506
75°	23316
80°	21913
85°	19176



TEST NUMBER: P250626

CATALOG NUMBER: LD8B100D010 ER8B100827 8LBN0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	903.3	9.6
10°-20°	2084.3	22.1
20°-30°	2484.1	26.3
30°-40°	1753.5	18.6
40°-50°	905.6	9.6
50°-60°	621.4	6.6
60°-70°	404.0	4.3
70°-80°	211.5	2.2
80°-90°	64.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5471.7	58.0
0°-40°	7225.3	76.6
0°-60°	8752.2	92.8
0°-90°	9432.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9432.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9895	
5°	9787	903
15°	7413	2084
25°	5498	2484
35°	2787	1754
45°	1132	906
55°	689	621
65°	406	404
75°	196	211
85°	54	64
90°	0	



TEST NUMBER: P250626

CATALOG NUMBER: LD8B100D010 ER8B100827 8LBN0MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	9895.4
1°	9901.5
2°	9901.5
3°	9886.4
4°	9853.3
5°	9787.0
6°	9669.7
7°	9525.2
8°	9326.6
9°	9085.9
10°	8815.0
11°	8529.1
12°	8231.1
13°	7945.2
14°	7668.4
15°	7412.6
16°	7174.8
17°	6955.1
18°	6756.4
19°	6569.8
20°	6389.3
21°	6211.7
22°	6037.2
23°	5862.6
24°	5685.1
25°	5498.5
26°	5287.7
27°	5059.0
28°	4809.3
29°	4544.5
30°	4243.4
31°	3951.6
32°	3653.5
33°	3346.6
34°	3063.7
35°	2786.9
37.5°	2145.9
40°	1652.3
42.5°	1330.3
45°	1131.6
47.5°	990.1
50°	878.8
52.5°	782.5
55°	689.2
57.5°	605.0



TEST NUMBER: P250626

CATALOG NUMBER: LD8B100D010 ER8B100827 8LBN0MW

CANDELA DISTRIBUTION (continued):

	0°
60°	535.7
62.5°	466.5
65°	406.3
67.5°	352.1
70°	282.9
72.5°	243.8
75°	195.7
77.5°	159.4
80°	123.4
82.5°	90.3
85°	54.2
87.5°	30.0
90°	0.0

(END OF REPORT)