

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246990

Luminaire Tested: **LSR8B80D010 EC8B809727 8LBMOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246990
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-81)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B80D010 EC8B809727 8LBM0LI
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 2700 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5989.1 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.75
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 74.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246990

CATALOG NUMBER: LSR8B80D010 EC8B809727 8LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P246990

CATALOG NUMBER: LSR8B80D010 EC8B809727 8LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81	77	75	73
6	90	82	76	72	89	81	76	72	79	75	71		78	74	71		77	73	70	69
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73	69	67	65
8	82	73	68	64	81	73	67	64	72	67	63		71	66	63		70	66	63	62
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		67	63	60	58
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		64	60	57	55

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P246990

CATALOG NUMBER: LSR8B80D010 EC8B809727 8LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	856.6	14.3
10°-20°	1877.7	31.4
20°-30°	1915.0	32.0
30°-40°	1072.5	17.9
40°-50°	228.7	3.8
50°-60°	28.3	0.5
60°-70°	7.4	0.1
70°-80°	1.8	0.0
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4649.3	77.6
0°-40°	5721.9	95.5
0°-60°	5978.9	99.8
0°-90°	5989.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5989.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9828	
5°	9382	857
15°	6760	1878
25°	4221	1915
35°	1700	1073
45°	254	229
55°	22	28
65°	8	7
75°	3	2
85°	3	1
90°	0	



TEST NUMBER: P246990

CATALOG NUMBER: LSR8B80D010 EC8B809727 8LBM0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	9828.1
2.5°	9717.4
5°	9382.5
7.5°	8843.7
10°	8178.7
12.5°	7465.1
15°	6760.5
17.5°	6051.7
20°	5400.0
22.5°	4793.6
25°	4221.3
27.5°	3620.5
30°	2986.2
32.5°	2323.4
35°	1700.2
37.5°	1139.1
40°	708.1
42.5°	423.3
45°	254.1
47.5°	141.3
50°	82.9
52.5°	43.9
55°	21.6
57.5°	15.3
60°	13.2
62.5°	6.3
65°	8.4
67.5°	8.4
70°	0.7
72.5°	2.1
75°	2.8
77.5°	1.4
80°	0.0
82.5°	0.7
85°	2.8
87.5°	0.0
90°	0.0

(END OF REPORT)