

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250395

Luminaire Tested: **LD8B100D010 ER8B100840 8LBN0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250395
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B100D010 ER8B100840 8LBN0B
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6381.0 lumens
Efficiency: N/A
Efficacy: 60.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 106.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250395

CATALOG NUMBER: LD8B100D010 ER8B100840 8LBN0B

Luminous Intensity Polar Plot





TEST NUMBER: P250395

CATALOG NUMBER: LD8B100D010 ER8B100840 8LBN0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		79	75	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	314413
5°	309389
10°	274885
15°	226757
20°	190975
25°	161077
30°	120603
35°	68253
40°	26986
45°	7243
50°	1386
55°	0
60°	204
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P250395

CATALOG NUMBER: LD8B100D010 ER8B100840 8LBN0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	915.3	14.3
10°-20°	1989.4	31.2
20°-30°	2135.7	33.5
30°-40°	1154.3	18.1
40°-50°	180.1	2.8
50°-60°	5.0	0.1
60°-70°	1.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5040.4	79.0
0°-40°	6194.7	97.1
0°-60°	6379.8	100.0
0°-90°	6381.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6381.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10196	
5°	9995	915
15°	7103	1989
25°	4734	2136
35°	1813	1154
45°	166	180
55°	0	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250395

CATALOG NUMBER: LD8B100D010 ER8B100840 8LBN0B

CANDELA DISTRIBUTION (FULL):

	0°
0°	10196.2
1°	10215.6
2°	10206.0
3°	10171.0
4°	10103.9
5°	9995.1
6°	9845.4
7°	9644.0
8°	9391.8
9°	9101.6
10°	8778.9
11°	8440.5
12°	8089.3
13°	7738.5
14°	7412.5
15°	7103.0
16°	6818.8
17°	6544.2
18°	6288.8
19°	6049.7
20°	5819.7
21°	5596.1
22°	5385.3
23°	5174.9
24°	4954.6
25°	4734.2
26°	4510.7
27°	4255.4
28°	3974.3
29°	3687.4
30°	3387.1
31°	3064.8
32°	2742.1
33°	2422.9
34°	2100.6
35°	1813.1
37.5°	1158.8
40°	670.4
42.5°	357.7
45°	166.1
47.5°	89.6
50°	28.9
52.5°	3.3
55°	0.0
57.5°	3.3



TEST NUMBER: P250395

CATALOG NUMBER: LD8B100D010 ER8B100840 8LBN0B

CANDELA DISTRIBUTION (continued):

	0°
60°	3.3
62.5°	0.0
65°	0.0
67.5°	3.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)