

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247060

Luminaire Tested: **LD8B100D010 ER8B100840 8LBWOLI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247060  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25264)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B100D010 ER8B100840 8LBW0LI  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 4000 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11509.1 lumens  
Efficiency: N/A  
Efficacy: 108.3 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.22  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 106.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P247060

CATALOG NUMBER: LD8B100D010 ER8B100840 8LBW0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P247060

CATALOG NUMBER: LD8B100D010 ER8B100840 8LBW0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	94	92
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	75	71	79	74	70	77	73	70	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51
8	72	61	54	49	71	60	54	49	59	53	49	58	52	48	57	52	48	47
9	68	56	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	198040
5°	201901
10°	210561
15°	222460
20°	230797
25°	232473
30°	221481
35°	195362
40°	157490
45°	111814
50°	67200
55°	30273
60°	7808
65°	1685
70°	829
75°	560
80°	284
85°	0



TEST NUMBER: P247060

CATALOG NUMBER: LD8B100D010 ER8B100840 8LBW0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	629.2	5.5
10°-20°	1970.1	17.1
20°-30°	3115.6	27.1
30°-40°	3201.4	27.8
40°-50°	1985.9	17.3
50°-60°	563.0	4.9
60°-70°	38.0	0.3
70°-80°	5.1	0.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5714.9	49.7
0°-40°	8916.4	77.5
0°-60°	11465.3	99.6
0°-90°	11509.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11509.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6422	
5°	6523	629
15°	6968	1970
25°	6833	3116
35°	5190	3201
45°	2564	1986
55°	563	563
65°	23	38
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P247060

CATALOG NUMBER: LD8B100D010 ER8B100840 8LBW0LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6422.3
2.5°	6434.6
5°	6522.6
7.5°	6626.0
10°	6724.6
12.5°	6846.5
15°	6968.4
17.5°	7037.8
20°	7033.2
22.5°	6965.3
25°	6832.6
27.5°	6592.0
30°	6220.2
32.5°	5731.2
35°	5189.7
37.5°	4577.3
40°	3912.4
42.5°	3221.1
45°	2564.0
47.5°	1953.1
50°	1400.8
52.5°	942.7
55°	563.1
57.5°	290.1
60°	126.6
62.5°	51.0
65°	23.1
67.5°	13.9
70°	9.2
72.5°	6.2
75°	4.7
77.5°	3.1
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)