

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247043

Luminaire Tested: **LSR8B90D010 EC8B909730 8LBN0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247043
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-80)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B90D010 EC8B909730 8LBN0LI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6610.9 lumens
Efficiency: N/A
Efficacy: 76.8 lumens/watt
Spacing Criteria (0/90/45): 0.47 / 0.47 / 0.56
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 86.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247043

CATALOG NUMBER: LSR8B90D010 EC8B909730 8LBN0LI

Luminous Intensity Polar Plot






TEST NUMBER: P247043

CATALOG NUMBER: LSR8B90D010 EC8B909730 8LBN0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95	95		
2	110	105	102	99	107	104	100	98	100	98	96	98	95	94	95	93	92	90	90	90	90	90		
3	105	100	95	92	103	98	94	91	96	92	90	93	91	88	91	89	87	85	85	85	85	85		
4	101	94	90	86	99	93	89	85	91	87	84	89	86	83	87	85	83	81	81	81	81	81		
5	97	90	85	81	95	89	84	80	87	83	80	85	82	79	84	81	78	77	77	77	77	77		
6	93	85	80	76	91	84	80	76	83	79	76	82	78	75	80	77	75	73	73	73	73	73		
7	89	81	76	72	88	81	76	72	79	75	72	78	74	72	77	74	71	70	70	70	70	70		
8	86	78	72	69	85	77	72	69	76	72	69	75	71	68	74	71	68	67	67	67	67	67		
9	82	74	69	66	81	74	69	66	73	69	65	72	68	65	71	68	65	64	64	64	64	64		
10	79	71	66	63	79	71	66	63	70	66	63	69	65	62	69	65	62	61	61	61	61	61		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P247043

CATALOG NUMBER: LSR8B90D010 EC8B909730 8LBN0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1377.4	20.8
10°-20°	2277.9	34.5
20°-30°	1920.4	29.0
30°-40°	871.4	13.2
40°-50°	152.1	2.3
50°-60°	8.3	0.1
60°-70°	1.2	0.0
70°-80°	1.4	0.0
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5575.6	84.3
0°-40°	6447.0	97.5
0°-60°	6607.4	99.9
0°-90°	6610.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6610.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16794	
5°	15840	###
15°	8040	2278
25°	4233	1920
35°	1339	871
45°	165	152
55°	7	8
65°	2	1
75°	0	1
85°	1	1
90°	0	



TEST NUMBER: P247043

CATALOG NUMBER: LSR8B90D010 EC8B909730 8LBN0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	16794.5
2.5°	16646.0
5°	15840.4
7.5°	14085.7
10°	11793.4
12.5°	9674.5
15°	8040.1
17.5°	6812.2
20°	5830.7
22.5°	4967.1
25°	4232.9
27.5°	3486.2
30°	2704.6
32.5°	1968.7
35°	1339.0
37.5°	822.2
40°	483.7
42.5°	283.7
45°	165.1
47.5°	98.7
50°	38.2
52.5°	5.8
55°	6.6
57.5°	5.8
60°	0.8
62.5°	0.8
65°	2.5
67.5°	0.0
70°	2.5
72.5°	4.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.8
87.5°	2.5
90°	0.0

(END OF REPORT)