

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243870

Luminaire Tested: **LD8B10D010 ER8B10827 8LBNOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243870
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10827 8LBN0LI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 2700 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1039.0 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243870

CATALOG NUMBER: LD8B10D010 ER8B10827 8LBN0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243870

CATALOG NUMBER: LD8B10D010 ER8B10827 8LBN0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	99	101	99	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91		94	92	89		92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		89	86	84	83
5	98	91	86	83	96	90	86	82	88	85	82		87	84	81		85	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78		83	80	77		82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74		80	77	74		79	76	74	72
8	88	80	75	72	86	79	75	71	78	74	71		77	74	71		76	73	71	70
9	85	77	72	69	84	76	72	69	75	71	68		75	71	68		74	70	68	67
10	82	74	69	66	81	73	69	66	73	69	66		72	68	66		71	68	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	156969
5°	109023
10°	57370
15°	36298
20°	26974
25°	21207
30°	15268
35°	6554
40°	2282
45°	877
50°	201
55°	75
60°	0
65°	102
70°	36
75°	83
80°	124
85°	0



TEST NUMBER: P243870

CATALOG NUMBER: LD8B10D010 ER8B10827 8LBN0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.4	27.2
10°-20°	328.1	31.6
20°-30°	283.1	27.3
30°-40°	122.8	11.8
40°-50°	19.2	1.9
50°-60°	1.4	0.1
60°-70°	0.8	0.1
70°-80°	0.8	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	893.6	86.0
0°-40°	1016.4	97.8
0°-60°	1037.0	99.8
0°-90°	1039.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1039.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5090	
5°	3522	282
15°	1137	328
25°	623	283
35°	174	123
45°	20	19
55°	1	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P243870

CATALOG NUMBER: LD8B10D010 ER8B10827 8LBN0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	5090.4
2.5°	4596.8
5°	3522.1
7.5°	2511.9
10°	1832.2
12.5°	1405.9
15°	1137.0
17.5°	956.3
20°	822.0
22.5°	707.5
25°	623.3
27.5°	534.5
30°	428.8
32.5°	298.1
35°	174.1
37.5°	97.2
40°	56.7
42.5°	35.2
45°	20.1
47.5°	16.2
50°	4.2
52.5°	2.1
55°	1.4
57.5°	0.7
60°	0.0
62.5°	0.4
65°	1.4
67.5°	1.1
70°	0.4
72.5°	1.8
75°	0.7
77.5°	0.0
80°	0.7
82.5°	0.4
85°	0.0
87.5°	0.7
90°	0.0

(END OF REPORT)