

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250619

Luminaire Tested: **LD8B100D010 ER8B100930 8LBM0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250619  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13928)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B100D010 ER8B100930 8LBM0B  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5726.1 lumens  
Efficiency: N/A  
Efficacy: 53.9 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.87  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 106.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250619

CATALOG NUMBER: LD8B100D010 ER8B100930 8LBM0B

### Luminous Intensity Polar Plot





TEST NUMBER: P250619

CATALOG NUMBER: LD8B100D010 ER8B100930 8LBM0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	74	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	60	58
9	76	66	61	57	75	66	60	57	65	60	56		64	60	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P250619

CATALOG NUMBER: LD8B100D010 ER8B100930 8LBM0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	652.6	11.4
10°-20°	1515.5	26.5
20°-30°	1922.7	33.6
30°-40°	1317.2	23.0
40°-50°	300.1	5.2
50°-60°	15.0	0.3
60°-70°	0.7	0.0
70°-80°	1.1	0.0
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4090.8	71.4
0°-40°	5408.0	94.4
0°-60°	5723.1	99.9
0°-90°	5726.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5726.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7430	
5°	7175	653
15°	5379	1516
25°	4259	1923
35°	2128	1317
45°	324	300
55°	6	15
65°	3	1
75°	0	1
85°	0	1
90°	0	



TEST NUMBER: P250619

CATALOG NUMBER: LD8B100D010 ER8B100930 8LBM0B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7429.8
1°	7468.6
2°	7454.6
3°	7399.3
4°	7305.2
5°	7175.2
6°	7017.5
7°	6834.8
8°	6632.8
9°	6416.9
10°	6212.2
11°	6024.0
12°	5822.0
13°	5675.4
14°	5520.5
15°	5379.3
16°	5252.0
17°	5127.5
18°	5011.3
19°	4897.8
20°	4795.4
21°	4690.3
22°	4582.3
23°	4488.3
24°	4383.1
25°	4258.7
26°	4120.2
27°	3959.8
28°	3788.2
29°	3597.3
30°	3387.0
31°	3149.0
32°	2902.7
33°	2645.3
34°	2382.5
35°	2127.9
37.5°	1502.6
40°	968.4
42.5°	570.0
45°	323.7
47.5°	174.3
50°	88.6
52.5°	16.6
55°	5.6
57.5°	2.8



TEST NUMBER: P250619

CATALOG NUMBER: LD8B100D010 ER8B100930 8LBM0B

**CANDELA DISTRIBUTION (continued):**

	0°
60°	0.0
62.5°	0.0
65°	2.8
67.5°	0.0
70°	0.0
72.5°	2.8
75°	0.0
77.5°	0.0
80°	2.8
82.5°	0.0
85°	0.0
87.5°	2.8
90°	0.0

(END OF REPORT)