

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250451

Luminaire Tested: **LD8B100D010 ER8B100930 8LBN0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250451
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B100D010 ER8B100930 8LBN0B
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5303.5 lumens
Efficiency: N/A
Efficacy: 49.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 106.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250451

CATALOG NUMBER: LD8B100D010 ER8B100930 8LBN0B

Luminous Intensity Polar Plot





TEST NUMBER: P250451

CATALOG NUMBER: LD8B100D010 ER8B100930 8LBNOB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72	79	75	71	77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250451

CATALOG NUMBER: LD8B100D010 ER8B100930 8LBN0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	760.7	14.3
10°-20°	1653.4	31.2
20°-30°	1775.1	33.5
30°-40°	959.4	18.1
40°-50°	149.7	2.8
50°-60°	4.1	0.1
60°-70°	1.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4189.3	79.0
0°-40°	5148.7	97.1
0°-60°	5302.5	100.0
0°-90°	5303.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5303.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8474	
5°	8307	761
15°	5904	1653
25°	3935	1775
35°	1507	959
45°	138	150
55°	0	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250451

CATALOG NUMBER: LD8B100D010 ER8B100930 8LBNOB

CANDELA DISTRIBUTION (FULL):

0°	
0°	8474.4
1°	8490.5
2°	8482.5
3°	8453.5
4°	8397.6
5°	8307.3
6°	8182.9
7°	8015.4
8°	7805.9
9°	7564.6
10°	7296.5
11°	7015.1
12°	6723.3
13°	6431.7
14°	6160.8
15°	5903.5
16°	5667.3
17°	5439.1
18°	5226.9
19°	5028.1
20°	4836.9
21°	4651.1
22°	4475.9
23°	4301.1
24°	4118.0
25°	3934.7
26°	3749.0
27°	3536.9
28°	3303.3
29°	3064.7
30°	2815.2
31°	2547.2
32°	2279.0
33°	2013.8
34°	1745.8
35°	1507.0
37.5°	963.2
40°	557.2
42.5°	297.3
45°	138.1
47.5°	74.4
50°	24.1
52.5°	2.7
55°	0.0
57.5°	2.7



TEST NUMBER: P250451

CATALOG NUMBER: LD8B100D010 ER8B100930 8LBN0B

CANDELA DISTRIBUTION (continued):

	0°
60°	2.7
62.5°	0.0
65°	0.0
67.5°	2.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)