

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244884

Luminaire Tested: **LD8B10D010 ER8B10830 8LBS0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244884  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B10D010 ER8B10830 8LBS0WMH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 3000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1165.0 lumens  
Efficiency: N/A  
Efficacy: 114.2 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244884

CATALOG NUMBER: LD8B10D010 ER8B10830 8LBS0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244884

CATALOG NUMBER: LD8B10D010 ER8B10830 8LBS0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55	64	58	54	63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	20367
5°	20306
10°	20124
15°	19924
20°	19709
25°	19397
30°	18864
35°	18005
40°	16685
45°	14090
50°	9667
55°	5333
60°	2683
65°	1510
70°	820
75°	584
80°	373
85°	248



TEST NUMBER: P244884

CATALOG NUMBER: LD8B10D010 ER8B10830 8LBS0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.2	5.3
10°-20°	176.0	15.1
20°-30°	262.0	22.5
30°-40°	297.7	25.6
40°-50°	243.3	20.9
50°-60°	95.3	8.2
60°-70°	22.2	1.9
70°-80°	5.3	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	500.2	42.9
0°-40°	797.9	68.5
0°-60°	1136.6	97.6
0°-90°	1165.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1165.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	660	
5°	656	62
15°	624	176
25°	570	262
35°	478	298
45°	323	243
55°	99	95
65°	21	22
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P244884

CATALOG NUMBER: LD8B10D010 ER8B10830 8LBS0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	660.5
2.5°	659.5
5°	656.0
7.5°	650.0
10°	642.7
12.5°	633.6
15°	624.1
17.5°	612.9
20°	600.6
22.5°	586.2
25°	570.1
27.5°	551.2
30°	529.8
32.5°	505.7
35°	478.3
37.5°	448.2
40°	414.5
42.5°	373.9
45°	323.1
47.5°	263.5
50°	201.5
52.5°	144.7
55°	99.2
57.5°	64.8
60°	43.5
62.5°	29.8
65°	20.7
67.5°	13.7
70°	9.1
72.5°	6.3
75°	4.9
77.5°	3.5
80°	2.1
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)