

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P249863

Luminaire Tested: **LD8B100D010 ER8B100930 8LBN0H**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P249863  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13959)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B100D010 ER8B100930 8LBN0H  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8089.2 lumens  
Efficiency: N/A  
Efficacy: 76.1 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.81  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 106.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P249863

CATALOG NUMBER: LD8B100D010 ER8B100930 8LBN0H

### Luminous Intensity Polar Plot





TEST NUMBER: P249863

CATALOG NUMBER: LD8B100D010 ER8B100930 8LBNOH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	65	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	55	63	58	54		62	57	54		61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P249863

CATALOG NUMBER: LD8B100D010 ER8B100930 8LBNOH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1011.7	12.5
10°-20°	2375.2	29.4
20°-30°	2596.0	32.1
30°-40°	1544.8	19.1
40°-50°	423.7	5.2
50°-60°	96.0	1.2
60°-70°	29.7	0.4
70°-80°	9.0	0.1
80°-90°	3.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5982.9	74.0
0°-40°	7527.8	93.1
0°-60°	8047.5	99.5
0°-90°	8089.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8089.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11095	
5°	10917	###
15°	8524	2375
25°	5735	2596
35°	2445	1545
45°	496	424
55°	96	96
65°	30	30
75°	8	9
85°	3	3
90°	0	



TEST NUMBER: P249863

CATALOG NUMBER: LD8B100D010 ER8B100930 8LBNOH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	11094.8
1°	11116.6
2°	11102.9
3°	11075.6
4°	11012.7
5°	10916.9
6°	10793.7
7°	10629.4
8°	10437.7
9°	10216.0
10°	9966.9
11°	9701.5
12°	9416.7
13°	9123.8
14°	8820.0
15°	8524.3
16°	8234.2
17°	7949.5
18°	7664.8
19°	7380.1
20°	7103.7
22.5°	6408.3
25°	5734.9
27.5°	4993.0
30°	4169.1
32.5°	3284.9
35°	2444.6
37.5°	1699.9
40°	1127.8
42.5°	739.1
45°	495.5
47.5°	328.5
50°	219.0
52.5°	134.2
55°	95.8
57.5°	68.4
60°	52.0
62.5°	38.3
65°	30.2
67.5°	19.2
70°	13.7
72.5°	11.0
75°	8.2
77.5°	5.5
80°	5.5



TEST NUMBER: P249863

CATALOG NUMBER: LD8B100D010 ER8B100930 8LBNOH

**CANDELA DISTRIBUTION (continued):**

	0°
82.5°	2.7
85°	2.7
87.5°	2.7
90°	0.0

(END OF REPORT)