

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246252

Luminaire Tested: **LD8B10D010 ER8B10830 8LBW0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246252
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10830 8LBW0B
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 705.0 lumens
Efficiency: N/A
Efficacy: 69.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246252

CATALOG NUMBER: LD8B10D010 ER8B10830 8LBW0B

Luminous Intensity Polar Plot





TEST NUMBER: P246252

CATALOG NUMBER: LD8B10D010 ER8B10830 8LBW0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101		101	99	98		97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86	84	81	80
4	96	88	83	78	94	87	82	78	85	80	77		83	79	76		81	78	75	74
5	91	82	76	72	89	81	76	71	80	75	71		78	74	70		76	73	70	68
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72	68	65	63
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67	63	60	58
8	77	67	61	57	76	67	61	57	66	60	56		65	60	56		64	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52		61	56	52		60	55	52	51
10	70	59	53	49	68	59	53	49	58	53	49		57	52	49		57	52	49	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	19880
5°	19380
10°	18865
15°	18513
20°	18032
25°	17393
30°	15959
35°	12234
40°	5821
45°	2215
50°	1084
55°	441
60°	111
65°	29
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P246252

CATALOG NUMBER: LD8B10D010 ER8B10830 8LBW0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.0	8.4
10°-20°	163.2	23.1
20°-30°	233.0	33.1
30°-40°	193.1	27.4
40°-50°	47.6	6.8
50°-60°	8.6	1.2
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	455.2	64.6
0°-40°	648.3	92.0
0°-60°	704.5	99.9
0°-90°	705.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	705.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	645	
5°	626	59
15°	580	163
25°	511	233
35°	325	193
45°	51	48
55°	8	9
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246252

CATALOG NUMBER: LD8B10D010 ER8B10830 8LBW0B

CANDELA DISTRIBUTION (FULL):

	0°
0°	644.7
2.5°	639.3
5°	626.1
7.5°	613.2
10°	602.5
12.5°	592.1
15°	579.9
17.5°	565.6
20°	549.5
22.5°	531.2
25°	511.2
27.5°	484.0
30°	448.2
32.5°	397.7
35°	325.0
37.5°	234.8
40°	144.6
42.5°	84.1
45°	50.8
47.5°	33.6
50°	22.6
52.5°	14.7
55°	8.2
57.5°	3.9
60°	1.8
62.5°	0.7
65°	0.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)