

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246540

Luminaire Tested: **LD8B10D010 ER8B10830 8LBW0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246540
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-48)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10830 8LBW0MW
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1112.0 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246540

CATALOG NUMBER: LD8B10D010 ER8B10830 8LBW0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246540

CATALOG NUMBER: LD8B10D010 ER8B10830 8LBW0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	86	83	80	78
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62
5	84	73	66	60	82	72	65	60	70	64	59	68	63	59	67	62	58	56
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47
8	69	58	50	45	68	57	50	45	56	50	45	55	49	45	54	48	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	40
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	22720
5°	22336
10°	21633
15°	21134
20°	20831
25°	20425
30°	19178
35°	15652
40°	9697
45°	6568
50°	5786
55°	5462
60°	5415
65°	5246
70°	4706
75°	4075
80°	3445
85°	2760



TEST NUMBER: P246540

CATALOG NUMBER: LD8B10D010 ER8B10830 8LBW0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.9	6.1
10°-20°	187.0	16.8
20°-30°	274.2	24.7
30°-40°	250.6	22.5
40°-50°	124.1	11.2
50°-60°	91.8	8.3
60°-70°	70.5	6.3
70°-80°	36.8	3.3
80°-90°	9.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	529.1	47.6
0°-40°	779.7	70.1
0°-60°	995.5	89.5
0°-90°	1112.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1112.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	737	
5°	722	68
15°	662	187
25°	600	274
35°	416	251
45°	151	124
55°	102	92
65°	72	71
75°	34	37
85°	8	9
90°	0	



TEST NUMBER: P246540

CATALOG NUMBER: LD8B10D010 ER8B10830 8LBW0MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	736.8
2.5°	732.9
5°	721.6
7.5°	706.4
10°	690.9
12.5°	675.8
15°	662.0
17.5°	649.0
20°	634.8
22.5°	619.0
25°	600.3
27.5°	574.5
30°	538.6
32.5°	488.1
35°	415.8
37.5°	326.2
40°	240.9
42.5°	182.3
45°	150.6
47.5°	133.3
50°	120.6
52.5°	110.4
55°	101.6
57.5°	94.2
60°	87.8
62.5°	81.1
65°	71.9
67.5°	62.1
70°	52.2
72.5°	43.0
75°	34.2
77.5°	26.5
80°	19.4
82.5°	13.4
85°	7.8
87.5°	2.8
90°	0.0

(END OF REPORT)