

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243882

Luminaire Tested: **LD8B10D010 ER8B10835 8LBN0LI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P243882  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B10D010 ER8B10835 8LBN0LI  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 3500 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1108.1 lumens  
Efficiency: N/A  
Efficacy: 108.6 lumens/watt  
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P243882

CATALOG NUMBER: LD8B10D010 ER8B10835 8LBN0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P243882

CATALOG NUMBER: LD8B10D010 ER8B10835 8LBN0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	100	108	104	101	99	101	99	96	98	96	94	95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91	94	92	89	92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83
5	98	91	86	83	96	90	86	82	88	85	82	87	84	81	85	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78	83	80	77	82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74	80	77	74	79	76	74	72
8	88	80	75	72	86	79	75	71	78	74	71	77	74	71	76	73	71	70
9	85	77	72	69	84	76	72	69	75	71	68	75	71	68	74	70	68	67
10	82	74	69	66	81	73	69	66	73	69	66	72	68	66	71	68	65	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	167395
5°	116264
10°	61181
15°	38708
20°	28766
25°	22616
30°	16283
35°	6987
40°	2435
45°	933
50°	216
55°	81
60°	0
65°	109
70°	36
75°	95
80°	142
85°	0



TEST NUMBER: P243882

CATALOG NUMBER: LD8B10D010 ER8B10835 8LBN0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	301.1	27.2
10°-20°	349.9	31.6
20°-30°	302.0	27.3
30°-40°	131.0	11.8
40°-50°	20.5	1.9
50°-60°	1.5	0.1
60°-70°	0.8	0.1
70°-80°	0.9	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	952.9	86.0
0°-40°	1083.9	97.8
0°-60°	1106.0	99.8
0°-90°	1108.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1108.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5428	
5°	3756	301
15°	1212	350
25°	665	302
35°	186	131
45°	21	21
55°	2	2
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P243882

CATALOG NUMBER: LD8B10D010 ER8B10835 8LBN0LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5428.5
2.5°	4902.0
5°	3756.0
7.5°	2678.7
10°	1953.9
12.5°	1499.2
15°	1212.5
17.5°	1019.8
20°	876.6
22.5°	754.5
25°	664.7
27.5°	570.0
30°	457.3
32.5°	317.9
35°	185.6
37.5°	103.7
40°	60.5
42.5°	37.6
45°	21.4
47.5°	17.3
50°	4.5
52.5°	2.3
55°	1.5
57.5°	0.8
60°	0.0
62.5°	0.4
65°	1.5
67.5°	1.1
70°	0.4
72.5°	1.9
75°	0.8
77.5°	0.0
80°	0.8
82.5°	0.4
85°	0.0
87.5°	0.8
90°	0.0

(END OF REPORT)