

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244458

Luminaire Tested: **LD8B10D010 ER8B10835 8LBS0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244458
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10835 8LBS0H
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1235.0 lumens
Efficiency: N/A
Efficacy: 121.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244458

CATALOG NUMBER: LD8B10D010 ER8B10835 8LBS0H

Luminous Intensity Polar Plot





TEST NUMBER: P244458

CATALOG NUMBER: LD8B10D010 ER8B10835 8LBSOH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69		76	72	68		74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56		65	59	55		63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50		60	54	50		59	54	50	48
8	70	58	51	46	69	58	51	46	57	50	46		55	50	46		54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	22100
5°	22027
10°	21859
15°	21705
20°	21560
25°	21275
30°	20616
35°	19455
40°	17680
45°	14548
50°	9695
55°	5054
60°	2381
65°	1248
70°	622
75°	429
80°	320
85°	248



TEST NUMBER: P244458

CATALOG NUMBER: LD8B10D010 ER8B10835 8LBSOH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.5	5.5
10°-20°	191.9	15.5
20°-30°	287.1	23.2
30°-40°	321.1	26.0
40°-50°	251.9	20.4
50°-60°	91.9	7.4
60°-70°	18.7	1.5
70°-80°	4.0	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	546.5	44.3
0°-40°	867.6	70.3
0°-60°	1211.4	98.1
0°-90°	1235.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1235.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	717	
5°	712	68
15°	680	192
25°	625	287
35°	517	321
45°	334	252
55°	94	92
65°	17	19
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P244458

CATALOG NUMBER: LD8B10D010 ER8B10835 8LBS0H

CANDELA DISTRIBUTION (FULL):

	0°
0°	716.7
2.5°	715.6
5°	711.6
7.5°	705.8
10°	698.1
12.5°	689.4
15°	679.9
17.5°	669.4
20°	657.0
22.5°	642.4
25°	625.3
27.5°	604.2
30°	579.0
32.5°	549.5
35°	516.8
37.5°	480.0
40°	439.2
42.5°	390.8
45°	333.6
47.5°	269.1
50°	202.1
52.5°	141.7
55°	94.0
57.5°	60.1
60°	38.6
62.5°	25.5
65°	17.1
67.5°	10.9
70°	6.9
72.5°	4.7
75°	3.6
77.5°	2.5
80°	1.8
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)