

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243810

Luminaire Tested: **LD8B10D010 ER8B10835 8LBWOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243810
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10835 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1201.0 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243810

CATALOG NUMBER: LD8B10D010 ER8B10835 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243810

CATALOG NUMBER: LD8B10D010 ER8B10835 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	21308
5°	21940
10°	23766
15°	26005
20°	27053
25°	26954
30°	25284
35°	21201
40°	14761
45°	8456
50°	4538
55°	1871
60°	469
65°	117
70°	63
75°	36
80°	53
85°	0



TEST NUMBER: P243810

CATALOG NUMBER: LD8B10D010 ER8B10835 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.3	5.8
10°-20°	229.6	19.1
20°-30°	361.2	30.1
30°-40°	343.6	28.6
40°-50°	158.4	13.2
50°-60°	36.0	3.0
60°-70°	2.4	0.2
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	660.1	55.0
0°-40°	1003.7	83.6
0°-60°	1198.1	99.8
0°-90°	1201.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1201.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	691	
5°	709	69
15°	815	230
25°	792	361
35°	563	344
45°	194	158
55°	35	36
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P243810

CATALOG NUMBER: LD8B10D010 ER8B10835 8LBW0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	691.0
1°	690.7
2°	692.0
3°	695.9
4°	701.9
5°	708.8
6°	717.3
7°	726.5
8°	736.0
9°	747.2
10°	759.0
11°	770.9
12°	783.4
13°	795.2
14°	806.0
15°	814.6
16°	820.8
17°	825.1
18°	827.1
19°	826.7
20°	824.4
21°	820.5
22°	815.6
23°	809.0
24°	801.4
25°	792.2
26°	781.4
27°	767.6
28°	751.1
29°	732.1
30°	710.1
32.5°	644.0
35°	563.2
37.5°	469.2
40°	366.7
42.5°	271.1
45°	193.9
47.5°	137.3
50°	94.6
52.5°	60.5
55°	34.8
57.5°	17.4
60°	7.6
62.5°	3.0
65°	1.6



TEST NUMBER: P243810

CATALOG NUMBER: LD8B10D010 ER8B10835 8LBW0LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.0
70°	0.7
72.5°	0.7
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)