

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244674

Luminaire Tested: **LD8B10D010 ER8B10835 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244674
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10835 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1102.1 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244674

CATALOG NUMBER: LD8B10D010 ER8B10835 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244674

CATALOG NUMBER: LD8B10D010 ER8B10835 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	24626
5°	24132
10°	23368
15°	23052
20°	22915
25°	22626
30°	21410
35°	17659
40°	11026
45°	7091
50°	5498
55°	4231
60°	3207
65°	2087
70°	893
75°	441
80°	195
85°	142



TEST NUMBER: P244674

CATALOG NUMBER: LD8B10D010 ER8B10835 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.3	6.7
10°-20°	204.0	18.5
20°-30°	303.9	27.6
30°-40°	282.2	25.6
40°-50°	133.3	12.1
50°-60°	71.6	6.5
60°-70°	28.7	2.6
70°-80°	4.5	0.4
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	581.2	52.7
0°-40°	863.4	78.3
0°-60°	1068.3	96.9
0°-90°	1102.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1102.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	799	
5°	780	73
15°	722	204
25°	665	304
35°	469	282
45°	163	133
55°	79	72
65°	29	29
75°	4	5
85°	0	0
90°	0	



TEST NUMBER: P244674

CATALOG NUMBER: LD8B10D010 ER8B10835 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	798.6
2.5°	793.1
5°	779.6
7.5°	762.4
10°	746.3
12.5°	733.1
15°	722.1
17.5°	710.7
20°	698.3
22.5°	684.0
25°	665.0
27.5°	638.2
30°	601.3
32.5°	547.1
35°	469.1
37.5°	369.5
40°	273.9
42.5°	204.0
45°	162.6
47.5°	135.9
50°	114.6
52.5°	95.6
55°	78.7
57.5°	64.1
60°	52.0
62.5°	40.6
65°	28.6
67.5°	16.8
70°	9.9
72.5°	5.9
75°	3.7
77.5°	2.2
80°	1.1
82.5°	0.7
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)