

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247080

Luminaire Tested: **LD8B100D010 ER8B100940 8LBW0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247080
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25264)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B100D010 ER8B100940 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 4000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10319.1 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.22
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 106.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247080

CATALOG NUMBER: LD8B100D010 ER8B100940 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P247080

CATALOG NUMBER: LD8B100D010 ER8B100940 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	94	92					92			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83					83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75					75			
4	93	84	78	73	91	83	77	72	81	75	71	79	74	70	77	73	70	68					68			
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62					62			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56					56			
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51					51			
8	72	61	54	49	71	60	54	49	59	53	49	58	52	48	57	52	48	47					47			
9	68	56	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43					43			
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39					39			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	177562
5°	181026
10°	188790
15°	199459
20°	206933
25°	208438
30°	198582
35°	175162
40°	141203
45°	100253
50°	60249
55°	27144
60°	7000
65°	1510
70°	748
75°	500
80°	249
85°	0



TEST NUMBER: P247080

CATALOG NUMBER: LD8B100D010 ER8B100940 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	564.1	5.5
10°-20°	1766.4	17.1
20°-30°	2793.5	27.1
30°-40°	2870.4	27.8
40°-50°	1780.6	17.3
50°-60°	504.8	4.9
60°-70°	34.1	0.3
70°-80°	4.6	0.0
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5124.0	49.7
0°-40°	7994.4	77.5
0°-60°	10279.8	99.6
0°-90°	10319.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10319.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5758	
5°	5848	564
15°	6248	1766
25°	6126	2793
35°	4653	2870
45°	2299	1781
55°	505	505
65°	21	34
75°	4	5
85°	0	1
90°	0	



TEST NUMBER: P247080

CATALOG NUMBER: LD8B100D010 ER8B100940 8LBW0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	5758.2
2.5°	5769.3
5°	5848.2
7.5°	5940.9
10°	6029.3
12.5°	6138.6
15°	6247.9
17.5°	6310.1
20°	6306.0
22.5°	6245.1
25°	6126.2
27.5°	5910.4
30°	5577.1
32.5°	5138.6
35°	4653.1
37.5°	4104.0
40°	3507.8
42.5°	2888.1
45°	2298.9
47.5°	1751.2
50°	1255.9
52.5°	845.2
55°	504.9
57.5°	260.1
60°	113.5
62.5°	45.7
65°	20.7
67.5°	12.4
70°	8.3
72.5°	5.6
75°	4.2
77.5°	2.8
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)